

TK60

Track KIT Track Lighting



Job Information

Project Name	
Type	
Location	
Quantity	
Date	

Description

Track kits are a ready solution for various track applications, providing all the components needed for quick installation. Track kits include the extruded aluminum track, Delta track heads with CCT selectable switch and a track center feed.

Features

Extrusion (TK60)

1/2" die cast aluminum construction with 3/4" PVC insulators holding 12 gauge flat conductor wiring. Polarity groove is located on face of track to indicate location of grounding conductor.

Electrical

System Electrical Rating: 20A, 120V, 60Hz

Note: Track lighting is a single circuit electrical distribution system designed to supply power to lighting units in flexible ways.

Compatibility

Liteline track system is compatible with all Liteline Track accessories and connectors.

1-Circuit Track

Single circuit track is available for 120V applications. Single hot and neutral conductors are rated for 20 Amps per branch circuit. Copper electrical conductors are concealed in an insulating thermo plastic low profile rack cross-section.

up to 12 watt LED module. It provides directional light source for specific aiming and assures a secure lock on the angle position. Includes a CCT selectable switch.

Center Feed (CF6108)

Low profile aesthetic design featuring solid 12-gauge conductors. The easy twist and lock feed and floating design allows it to be installed anywhere along the track. Complete with canopy cover and mounting hardware.

Track Fixtures (DA2012 - Delta)

Aluminum designer track fixture with




SPECIFICATION

Application	Track
Approved Location	Dry / Indoor
Beam Angle	38°
CCT	2700 K - 3000 K - 3500 K - 4000 K - 5000 K
Certification	cETLus
Colour	BK / WH
CRI	90
Dimming	Yes
Dimming Tech	TRIAC/ELV
Energy Star	Yes
LM80	Yes
Lumens	Up to 1010
Lumens per Watt	Up to 84
Power Factor	≥0.97
Primary Voltage	120
Projected Life	50,000 hrs
Rotation	358°
Tilt	90°
TM-30 Annex E	P2V-/F2
Warranty	5 Years
Wattage	12W

Color Temp.	Lumens per Head
2700 K	Up to 890
3000 K	Up to 940
3500 K	Up to 990
4000 K	Up to 1010
5000 K	Up to 1005

Technical Drawings



Model	Length (L)
TK6002	24" (610mm)
TK6004	48" (1219mm)
TK6006	72" (1829mm)

Ordering Guide



TK6002-BK-KIT

2' Extrusion, center feed, 2 x DA2012 track fixtures, black.



TK6004-BK-KIT

4' Extrusion, center feed, 3 x DA2012 track fixtures, black.



TK6006-BK-KIT

6' Extrusion, center feed, 5 x DA2012 track fixtures, black.



TK6002-WH-KIT

2' Extrusion, center feed, 2 x DA2012 track fixtures, white.



TK6004-WH-KIT

4' Extrusion, center feed, 3 x DA2012 track fixtures, white.



TK6006-WH-KIT

6' Extrusion, center feed, 5 x DA2012 track fixtures, white.

Length	Color	Kit Style
TK600 -		
2: 2' Track w/Center Feed	BK : Black	KIT Ships components all together
4: 4' Track w/Center Feed	WH : White	KIT2 Ships in 1 Kit per box
6: 6' Track w/Center Feed		

Notes: Due to our continued efforts to improve our products, product specifications are subject to change without notice.