

Individual Spec Sheet

VTL4 GEN. 3

3 CCT AND 3 POWER SELECT, NEMA 4X, NSF VAPOR TIGHT

ORDERING INFORMATION

Order Code: 70483
Model Number: VTL4-3-PS2-Q-3C
UPC: 069549035133
Case Quantity: 1
DLC Unique ID: To be advised

PHYSICAL DATA

Lens Material: Frosted PC
Latch Material: Stainless steel
Housing Material: Polycarbonate
Mounting: Surface, suspended

PERFORMANCE DATA

Watts (W): 30/45/60
Volts (V AC): 120-347
Color Temperature (K)¹: 3 CCT (3 500, 4 000, 5 000)
Lumen Output (lm)²: 4 500-9 000
Efficacy (lm/W): 145-154
CRI: 80+
Life L70 (h)³: 54 000
Tested LM-80 (h)³: 54 000
Dimming: 0-10 V
Power Factor: ≥ 0.9
THD (%): ≤ 20
Frequency (Hz): 50/60
Operating Temp. Range: -40 °C to +40 °C (-40 °F to +104 °F)

¹ Typical colour temperature range: +/- 5 %

² Lumen values are derived from photometric testing. Initial lumens range: +/- 10 %

³ Life hours are derived from IESNA LM-80 testing report and projected per IESNA TM-21 extrapolations

LUMEN SPECIFICATION TABLE

Watts (W)	3 500 K		4 000 K		5 000 K	
	Lumen output (lm)	Efficacy (lm/W)	Lumen output (lm)	Efficacy (lm/W)	Lumen output (lm)	Efficacy (lm/W)
30	4 500	150	4 620	154	4 530	151
45	6 615	147	6 840	152	6 660	148
60	8 700	145	9 000	150	8 760	146

DEFAULT PROGRAMMING

60 W / 4 000 K

This lighting equipment complies with Canadian standard ICES-005 for use in residential applications.
 Data is based upon tests performed in a controlled environment.
 Actual performance can vary depending on operating conditions. Specifications are subject to change without notice.



ACCESSORIES (order separately)

Order code	Type
69589	90° Angle Brackets (2pcs)
70510	Tamper proof brackets 4' (2pcs)
69668 ¹	Junction box bracket (1pc)
69588	Replacement surface mounting brackets and V-Hooks (2pcs)
70539	Replacement 4ft frosted polycarbonate lens
70484	Replacement stainless steel latch kit with hole (10pcs)
70403	Replacement hardware kit: watertight end caps (2pcs), watertight glands (2pcs), surface mount brackets (2pcs), V-hooks (2pcs) and mounting hardware
70404	Replacement watertight gland (1pc)
70405	Replacement watertight end cap (1pc)
70541	Replacement for 30/45/60W driver (1pc)
70543 ²	Replacement for 30/45/60W internal module (1pc)

¹ Accessory requires additional center hole (CH) on top of housing. Fixture maintains wet location status, however NEMA 4X and IP ratings are not applicable with CH. Please see installation instructions for more details

² Replacement for internal module includes all internal components (gear tray, driver, LED boards and wires)

SMART ACCESSORIES (order separately)

Order code	Type
69733	Genio Bluetooth® Mesh internal integrated fixture adapter
70222	Genio Bluetooth® Mesh kit internal high frequency sensor (69732) and integrated fixture adapter (69733)


COMPATIBLE DIMMERS¹

Brand	Model
Leviton	DS710-10Z, DD710-BDZ, IP710-LFZ
Lutron	DVSTV-453P, MAESTRO MS-Z101


Dimming range: 10 %-100 %

¹ This table shows dimmers that have been tested and have demonstrated proper operation under normal conditions. Each installation being unique, various factors such as load, common neutrals or other electrical products on the circuit can, in certain instances, cause variance in system performance. Read and comply to the dimmer installation instructions. Consult dimming system manufacturer for additional support in operation. Some dimmers may require more than one product for stable operation. Stanpro recommends to use dimmers designed to work with LED products. Older dimmers designed for incandescent products may cause erratic operation.

DIMENSIONS



Data is based upon tests performed in a controlled environment. Actual performance can vary depending on operating conditions. All products are subject to change or may be discontinued any time without notice.


PHOTOMETRIC DATA¹
70483 • VTL4-3-PS2-Q-3C • 30 W • 4 000 K • 4 710 lm
Polar candela distribution

Zonal lumen summary

Zone	Lumens	% Fixture
0-30	1 071.4	22.8
0-40	1 757.1	37.3
0-60	3 154.6	67
60-90	1 249.5	26.5
70-100	837.2	17.8
90-120	271.0	5.8
0-90	4 404.1	93.5
90-180	305.4	6.5
0-180	4 709.5	100

Illuminance at a distance

Center beam fc	Beam width
1.7'	478
3.3'	127
5.0'	55.3
6.7'	30.8
8.3'	20.1
10.0'	13.8

Vert. spread: 107.4°
Horiz. spread: 129.5°


70483 • VTL4-3-PS2-Q-3C • 45 W • 4 000 K • 6 920 lm
Polar candela distribution

Zonal lumen summary

Zone	Lumens	% Fixture
0-30	1 575.4	22.8
0-40	2 583.6	37.3
0-60	4 639.4	67
60-90	1 834.5	26.5
70-100	1 227.5	17.7
90-120	395.5	5.7
0-90	6 473.9	93.6
90-180	446.0	6.4
0-180	6 919.9	100

Illuminance at a distance

Center beam fc	Beam width
1.7'	703
3.3'	187
5.0'	81.3
6.7'	45.3
8.3'	29.5
10.0'	20.6

Vert. spread: 107.4°
Horiz. spread: 129.0°

70483 • VTL4-3-PS2-Q-3C • 60 W • 4 000 K • 8 759 lm
Polar candela distribution

Zonal lumen summary

Zone	Lumens	% Fixture
0-30	1 992.1	23.3
0-40	3 267.4	38.1
0-60	5 867.8	68.1
60-90	2 323.9	26.1
70-100	1 555.8	17.1
90-120	503.2	5.2
0-90	8 191.7	94.1
90-180	566.9	5.9
0-180	8 758.6	100

Illuminance at a distance

Center beam fc	Beam width
1.7'	888
3.3'	236
5.0'	103
6.7'	57.2
8.3'	37.3
10.0'	25.7

Vert. spread: 107.5°
Horiz. spread: 129.3°

¹ Complete IES files available on our website.

Data is based upon tests performed in a controlled environment. Actual performance can vary depending on operating conditions.
All products are subject to change or may be discontinued any time without notice.