




UNIVERSAL GROUND BAR - RGRB19U (QTY. 1) INCLUDES:
-#12-24 HEX HEAD SCREWS (QTY. 20) PRE ASSEMBLED




#12 FLAT WASHER (QTY. 2)




#12-24 SLOTTED HEX-HEAD ZINC PLATED
THREAD FORMING SCREW (QTY. 2)



#10-32 SLOTTED HEX-HEAD ZINC PLATED
THREAD FORMING SCREW (QTY. 2)



M5 SLOTTED HEX-HEAD ZINC PLATED
THREAD FORMING SCREW (QTY. 2)



M6 SLOTTED HEX-HEAD ZINC PLATED
THREAD FORMING SCREW (QTY. 2)

NOTES:

- MATERIAL:
GROUND BAR: COPPER, TIN PLATED
HARDWARE: STEEL, ZINC PLATED
- PACKAGING: 1 KIT PER BOX
- DIMENSIONS IN BRACKETS ARE MILLIMETERS
- ALL COMPONENTS THAT MAKE UP THIS KIT ARE RoHS COMPLIANT



LISTED
GROUNDING AND BONDING EQUIPMENT



CERTIFIED

PART NUMBER		RGRB19U	
TITLE		GROUNDING BUSBAR KIT	
CUSTOMER DRAWING			
ITEM REVISION NAME	N41661BB/06		
DATASET FILE NAME	N41661BB-DS/06B		
THIRD ANGLE PROJECTION			
MATERIAL	SEE NOTES		DRAWING NUMBER
			N41661BB-DC
DRAWN BY	DATE	CHK	SCALE
JHNU	1-06	LEM	NONE
SHEET 1 OF 1			SIZE
			B

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
06B	3-7-25	JHNU	JHNU	JSUN	D. REMOVED CE LOGO FROM DRAWING	011470
06A	5-21-24	JHNU	JHNU	MRWA	C. REVISED DRAWING NUMBER: N41661BB-DC WAS C41661 B. REVISED NOTES TO ADD MATERIAL A. CONVERTED TO NX	004182

B-SIZE CUSTOMER