

2


1

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT PART #	WIRE SIZE AWG	DIMENSIONS - in [mm]			
		A ± .03 [0,8]	B ± .01 [0,3]	C ± .01 [0,3]	D ± .03 [0,8]
BSN22J	26-22	.79 [20,1]	.08 [2,0]	.04 [1,0]	.47 [11,9]

INSTALLATION TOOL

CT-1300



## NOTES:

## 1. RECOMMENDED FOR:

- A. #26-22 AWG SOLID OR STRANDED COPPER WIRE  
 B. 221°F [105°C] MAX TEMP. RATING  
 C. 600V MAX VOLTAGE RATING

## 2. MATERIAL:

- A. STAMPING: .02" [0,5] THK COPPER, TIN PLATED  
 B. HOUSING: NYLON, YELLOW

3. SEE [www.panduit.com](http://www.panduit.com) FOR PACKAGE QUANTITIES

## 4. DIMENSIONS IN BRACKETS ARE IN MILLIMETERS

5. WIRE STRIP LENGTH:  $1/4" \begin{smallmatrix} +1/32 \\ -0 \end{smallmatrix}$  [6,4mm  $\begin{smallmatrix} +0,8 \\ -0 \end{smallmatrix}$ ]

TITLE			
BUTT SPLICE, NYLON INSULATED #26-22 AWG			
CUSTOMER DRAWING			
ITEM REVISION NAME		03365NBB/00	
DATASET FILE NAME		03365NBB-DC/00A	
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]		MATERIAL:	
.x ± .1 [2.54] .xx ± .01 [.25]		.xxx ± .005 [.127] ANGLES ± 5°	
THIRD ANGLE PROJECTION		SEE NOTES	
DRAWN BY JHNU		DATE 9-18-24	
CHK JHNU		SCALE NONE	
DRAWING NUMBER: 03365NBB-DC		SHT 1 OF 1	
REV		A	

2

1

91/0100DA/16