

A30QS

Amp-Trap® Form 101

HIGH SPEED FUSES



A30QS Amp-Trap® high speed fuses are intended for the protection of Power Semiconductors such as diodes, phase control SCRs and other power semiconductor devices. The A30QS is recommended for new applications providing solutions for your critical protection needs at 300V and less semiconductors.

FEATURES/BENEFITS

- Low I^2t minimizes damage to protected component on short circuit
- Controlled arc voltage reduces stress to circuit components during fuse clearing
- Choice of mounting types helps in equipment design

Catalog Numbering System					
A	30	QS	600	- 4	TI
Amp-Trap® Fuse	Rated Volts - 300	Style	Amperes*	Mounting Types*	Integral Blown-Fuse Indicator
				Ferrule: 1 Blades, bolt-in: 4 Hockey puck, bolt-in: 128	Trigger Indicator: TI IL Indicator: IL

* For ampere ratings and styles not listed, call Technical Services at 978-248-8914.

RATINGS

- **Volts:** 300VAC / DC
- **Amps:** 1 to 4500A
- **I.R.:** 200kA I.R. AC, 100kA I.R. DC
- **L/R:** 10ms

HIGHLIGHTS

- Fast acting
- Current-limiting
- Low I^2t
- Indicator options available
- Superior DC capabilities

APPLICATIONS

- Protection of 300V (or less) heavy duty rectifiers and similar heavy duty power supplies

APPROVALS/STANDARDS

- UL recognized component
UL File E60314
- AC: UL guide no. JFHR2 (35-4500A)



SINGLE POLE FUSE BLOCKS FOR A30QS FUSES

Fuse Ampere Rating	Catalog No.
1-30	70316 + US14
31-60	P243G
61-100	P243
101-200	P243
401-600	P243G
700-800	1SC375



CATALOG NUMBERS (AMPS)

Catalog No.	Dimen. Fig.	Catalog No.	Dimen. Fig.	Catalog No.	Dimen. Fig.	Catalog No.	Dimen. Fig.
A30QS1-1	1	A30QS60-4	2	A30QS300-4TI	3	A30QS1000-128IL	5
A30QS2-1	1	A30QS70-4	3	A30QS350-4	3	A30QS1200-128	5
A30QS3-1	1	A30QS80-4	3	A30QS400-4	3	A30QS1500-128	6
A30QS4-1	1	A30QS90-4	3	A30QS400-4IL	4	A30QS1500-128IL	7
A30QS5-1	1	A30QS100-4	3	A30QS400-4TI	3	A30QS1600-128	6
A30QS6-1	1	A30QS100-4TI	3	A30QS450-4	3	A30QS2000-128	6
A30QS7-1	1	A30QS125-4	3	A30QS500-4	3	A30QS2000-128IL	7
A30QS8-1	1	A30QS130-4	3	A30QS550-4	3	A30QS2500-128	6
A30QS10-1	1	A30QS150-4	3	A30QS600-4	3	A30QS2500-128IL	7
A30QS12-1	1	A30QS150-4TI	3	A30QS600-4TI	3	A30QS3000-128	6
A30QS15-1	1	A30QS175-4	3	A30QS600-4IL	4	A30QS3500-128	6
A30QS20-1	1	A30QS200-4	3	A30QS700-4	4	A30QS3500-128IL	7
A30QS25-1	1	A30QS200-4TI	3	A30QS700-128	5	A30QS4000-128	6
A30QS30-1	1	A30QS225-4	3	A30QS800-4	3	A30QS4500-128	6
A30QS35-4	2	A30QS250-4	3	A30QS800-4IL	4		
A30QS40-4	2	A30QS250-4TI	3	A30QS800-128	5		
A30QS50-4	2	A30QS300-4	3	A30QS1000-128	5		

* For ampere ratings and styles not listed, call Technical Services at 978-248-8914.

DIMENSIONS

Outline Ref.	Mounting Type	Fig.	Dimensions - Inches (mm)								Tap
			A	B	C	D	E	F	G	H	
A30QS1 to 30	1	1	2.00 (51)	0.56 (14)	-	-	-	-	-	-	-
A30QS35 to 60	4	2	3.19 (81)	0.83 (21)	1.63 (41)	2.50 (64)	2.25 (58)	0.34 (9)	.72 (18)	0.13 (3)	-
A30QS70 to 200	4	3	3.13 (80)	1.22 (31)	1.63 (41)	2.44 (62)	2.19 (55)	0.31 (8)	.75 (31)	0.19 (5)	-
A30QS225 to 700	4, 4IL*	3,4*	3.84 (98)	1.50 (38)	1.59 (40)	3.10 (74)	2.28 (58)	0.41 (10)	1.00 (25)	0.25 (6)	-
A30QS700 to 1200	128	5	2.59 (66)	2.875 (73)	2.34 (59)	2.50 (64)	1.50 (38)	-	-	-	3/8-24-1/2 Deep (2)
A30QS1500 to 2500	128, 128IL*	6, 7*	2.59 (66)	3.50 (89)	2.34 (59)	3.00 (64)	1.50 (38)	1.50 (38)	-	-	3/8-24-1/2 Deep (4)
A30QS3000 to 4500	128, 128IL*	6, 7*	2.59 (66)	4.50 (114)	2.34 (59)	3.75 (95)	1.50 (38)	1.50 (38)	-	-	1/2-20-1/2 Deep (4)
A30QS3000 to 4500	128, 128IL*	6, 7*	2.59 (66)	4.50 (114)	2.34 (59)	3.75 (95)	1.50 (38)	1.50 (38)	-	-	1/2-20-1/2 Deep (4)

* Optional (IL) indicator.

