

A15QS

Amp-Trap® Form 101

HIGH SPEED FUSES



A15QS Amp-Trap® Form 101 high speed fuses were designed for the specific protection of diodes and other semiconductor devices rated 150VAC/DC. The A15QS product line's compact design is perfect for those applications that have limitations on available space.

FEATURES/BENEFITS

- Low I^2t minimizes damage to protected components on short circuit
- Controlled arc voltage reduces stress to circuit components during fuse clearing
- Choice of mounting types provides options for unique termination requirements

Catalog Numbering System					
A	15	QS	400	- 4	TI
Amp-Trap® Fuse	Rated Volts - 150	Style	Amperes	Mounting Types* Ferrule: 1 Ferrule, midjet dims (10x38mm): 2 Blades, bolt-in: 4 Hockey puck, bolt-in: 128	Integral Blown-Fuse Indicator Trigger Indicator: TI IL Indicator: IL

* For harsh duty applications, please contact Technical Services at 978-248-8914.

RATINGS

- **Volts:** 150VAC / DC
- **Amps:** 1 to 6000A
- **I.R.:** 100kA I.R. AC, 50kA I.R. DC

HIGHLIGHTS

- Fast acting
- Current limiting
- Low I^2t
- Indicator options available

APPLICATIONS

- Protection of heavy duty devices such as electrochemical rectifiers

APPROVALS/STANDARDS

- UL recognized component
UL File E60314
- AC: UL guide no. JFHR2 (1-4000A)
- DC tested to UL standard 198L parameters (1-4000A)



SINGLE POLE FUSE BLOCKS FOR A15QS FUSES

Fuse Ampere Rating	Catalog No.	
1-30	30311	
31-60	U71006	
500-600	P243G	
40-450	P243D	
800	1SC375	

CATALOG NUMBERS (AMPS)

Catalog No.	Dimen. Fig.	Catalog No.	Dimen. Fig.	Catalog No.	Dimen. Fig.	Catalog No.	Dimen. Fig.
A15QS1-2	1	A15QS60-1	1	A15QS300-4TI	2	A15QS1200-128	4
A15QS2-2	1	A15QS70-4	2	A15QS300-4IL	3	A15QS1200-128IL	5
A15QS3-2	1	A15QS70-4TI	2	A15QS350-4	2	A15QS1500-128	4
A15QS4-2	1	A15QS80-4	2	A15QS350-4TI	2	A15QS1500-128IL	5
A15QS5-2	1	A15QS80-4TI	2	A15QS400-4	2	A15QS2000-128	4
A15QS6-2	1	A15QS90-4	2	A15QS400-4IL	3	A15QS2000-128IL	5
A15QS7-2	1	A15QS100-4	2	A15QS400-4TI	2	A15QS2500-128	4
A15QS8-2	1	A15QS100-4TI	2	A15QS450-4	2	A15QS2500-128IL	5
A15QS10-2	1	A15QS130-4	2	A15QS450-4IL	3	A15QS3000-128	4
A15QS12-2	1	A15QS130-4TI	2	A15QS500-4	2	A15QS3000-128IL	5
A15QS15-2	1	A15QS150-4	2	A15QS500-4IL	3	A15QS3500-128	6
A15QS20-2	1	A15QS150-4IL	3	A15QS600-4	2	A15QS4000-128	6
A15QS25-2	1	A15QS150-4TI	2	A15QS600-4IL	3	A15QS4000-128IL	7
A15QS30-2	1	A15QS175-4	2	A15QS700-4	2	A15QS4500-128	8
A15QS35-1	1	A15QS175-4TI	2	A15QS800-4	2	A15QS4500-128IL	8
A15QS40-1	1	A15QS200-4	2	A15QS1000-4	2	A15QS5000-128	8
A15QS40-4TI	2	A15QS200-4IL	3	A15QS1000-4IL	3	A15QS6000-128	8
A15QS45-1	1	A15QS250-4	2	A15QS1000-4TI	2		
A15QS50-1	1	A15QS250-4TI	2	A15QS1000-128	4		
A15QS50-4	2	A15QS300-4	2	A15QS1000-128IL	5		

* For ampere ratings and styles not listed, call Technical Services at 978-248-8914.

DIMENSIONS

Outline Ref.	Mounting Type	Fig.	Dimensions - Inches (mm)								Tap
			A	B	C	D	E	F	G	H	
A15QS1 to 30	2	1	1.50 (38.1)	0.41 (10.4)	-	-	-	-	-	-	-
15QS35 to 60	1	1	2.00 (50.8)	0.81 (20.6)	-	-	-	-	-	-	-
A15QS20 to 450	4, 4TI*, 4IL*	2, 3*	2.66 (67.6)	1.00 (25.4)	1.16 (29.5)	2.19 (55.6)	1.88 (47.6)	0.31 (7.9)	0.74 (18.8)	0.125 (3.2)	-
A15QS500 to 1000	4, 4TI*, 4IL*	2, 3*	3.50 (88.9)	1.50 (38.1)	1.25 (31.8)	2.56 (65.0)	1.94 (49.3)	0.41 (10.4)	1.00 (25.4)	0.25 (6.4)	-
A15QS750 to 2000	128, 128IL	4, 5*	1.88 (47.8)	2.00 (50.8)	1.63 (41.4)	1.75 (44.5)	1.00 (25.4)	-	-	-	3/8-24-1/2 Deep
A15QS2500 to 3000	128, 128IL	4, 5*	1.88 (47.88)	3.00 (76.2)	1.63 (41.4)	2.50 (63.5)	1.50 (38.1)	-	-	-	1/2-20-1/2 Deep
A15QS3500 to 4000	128, 128IL	6, 7*	1.88 (47.88)	3.50 (88.9)	1.63 (41.4)	3.00 (76.2)	1.06 (27.0)	1.06 (27.0)	-	-	1/2-20-1/2 Deep
A15QS4500 to 6000	128	8	2.38 (60.5)	5.75 (146)	1.88 (47.7)	5.00 (127)	1.50 (38.1)	1.50 (38.1)	-	-	1/2-20-1/2 Deep

* Optional Trigger Indicator (TI) and/or (IL) indicator.

