



Rated for 50A and 125/250V, this single electrical outlet is perfect for use with Electrical Vehicle (EV) chargers in indoor and outdoor applications. Built for use with up-to Level 2 plug-in EV chargers, this outlet is capable of withstanding high temperatures to support safe, long-lasting EV charging at home. Features weather-resistance for code compliance and additional safety. Offering easy installation, this EV outlet provides homeowners with the perfect opportunity to use a plug-in charger.

## Features & Benefits

Built specifically for use with plug-in EV chargers in residential spaces to optimize charging for safety and efficiency

Capable of withstanding high temperatures associated with EV charging created by ambient conditions and current draw compared with products made from PVC

Weather-resistant for outdoor use providing power access to EV chargers; NEMA compliant

Manufactured with high-quality materials for lasting durability and reliable use

Installs easily as a straight-blade, 3-pole, 4-wire receptacle for secure EV charging

With its robust design and performance, the 50A Weather Resistant Heavy-Duty Flush Mount Receptacle can sustain the necessary extended charge time and high frequency of insertions EV chargers require.

## Specifications

### General Info

|                     |                         |                       |                      |
|---------------------|-------------------------|-----------------------|----------------------|
| Product Line        | Pass & Seymour          | Color                 | Black                |
| Finish              | Satin                   | UPC Number            | 785007454697         |
| Country Of Origin   | China                   | Number of Receptacles | 1                    |
| Outlet Type         | Weather-Resistant       | Application Sector    | Commercial           |
| Wall Plate Included | No                      | Standard              | UL, CSA, RoHS, cULus |
| Warranty Type       | 1-Year Limited Warranty |                       |                      |

### Dimensions

|                  |         |                   |         |
|------------------|---------|-------------------|---------|
| Product Width US | 2.55 in | Product Weight US | 0.34 lb |
|------------------|---------|-------------------|---------|

|                   |         |                   |        |
|-------------------|---------|-------------------|--------|
| Product Height US | 3.77 in | Product Length US | 2.2 in |
|-------------------|---------|-------------------|--------|

Listing Agencies / 3rd Party Agencies

|            |     |
|------------|-----|
| ETL Listed | Yes |
|------------|-----|

Additional Information

|                |     |
|----------------|-----|
| RoHS Compliant | Yes |
|----------------|-----|

Technical Information

|                      |                 |                         |            |
|----------------------|-----------------|-------------------------|------------|
| Connection Location  | Side Only       | Number of USBs          | 0          |
| Number of Wires      | 4               | Amperage                | 50 A       |
| Indoor/Outdoor       | Both            | NEMA Configuration Code | NEMA 14-50 |
| Wire Connection Type | Screw Terminals | Voltage                 | 125/250 V  |