



Insulated Metallic Grounding Bushings

With Aluminum Lay-In Lug - Zinc Die Cast

Features

- Tin plated aluminum alloy 6061-T6 rated for AL and CU conductor
- Liner is rated flame retardant to 105°C
- cUL listed for use with copper or aluminum grounding conductor

Applications


- Use to provide a means of grounding Rigid or IMC conduit
- Indoor or outdoor use (lay-in lug)
- Use with locknut to terminate service conduit to a cabinet
- Lug provided for bonding jumper to a neutral bus bar
- Round surface of bushing prevents damage to wire insulation
- Plastic liner prevents damage to wire insulation

Standard Material

- Body - Zinc die cast, Plastic insulator, Aluminum Lug, Clamping & set screw - Steel

Certification

- UL File #: E515752



Catalog Number	UPC	Size	Grounding Lug Wire Size		Box Qty	Ship Case	Weight (lbs) per 100	Inches	
			Min.	Max.				A	B
321	11913	1/2"	14	4	50	500	5	1.04	0.38
322	11914	3/4"	14	4	50	500	7	1.26	0.41
323	11916	1"	14	4	25	250	10	1.53	0.50
324	11917	1-1/4"	14	4	25	250	16	1.86	0.53
325	11918	1-1/2"	14	4	10	100	19	2.13	0.56
326	11919	2"	14	4	10	100	25	2.60	0.66
327	11921	2-1/2"	14	1/0	25	---	38.5	3.15	0.75
328	11923	3"	14	1/0	10	---	43.8	3.76	0.75
329	11925	3-1/2"	14	1/0	10	---	47.8	4.27	0.75
330	11926	4"	14	1/0	10	---	55.7	4.76	0.75
330AM	11927	5"	#6	250MCM	10	---	250	6.10	1.14
330BM	11928	6"	#6	250MCM	10	---	350	7.15	1.14

Nesco Inc.

1039 Cardiff Blvd., Mississauga, ON L5S 1P4
 TF: (866) 466-3726 Tel: (905) 793-2218 Fax: (905) 793-2268
www.nescocanada.com