

# 24-Port PoE Cloud-Managed Gigabit Switch

SML-28GPA



## Key Features

- Layer 2 Network Management PoE Ethernet Switch
- Twenty-Four (24) Gigabit PoE Ports and Four (4) Uplink Ports (Two (2) SFP Ports, Two (2) RJ-45 Ports)
- Total PoE Budget: 375 W
- Supports IEEE802.3af, IEEE802.3at, and IEEE802.3bt Standards
- Web-Based and Cloud-Based Management Interface
- Extendable PoE Signal Up to 820 ft (250 m) at 10 Mbps
- Switching Capacity: 56 Gbps

## Certifications

- NDAA Compliant
- FCC

## Key Technologies

### Intelligent PoE

This switch lets users control power consumption and monitor power consumption changes in real time. This feature prioritizes the most important ports while preventing malfunction during power consumption rate changes.

### PoE Watchdog

This switch includes PoE watchdog capabilities to ensure the switch is running properly at all times. The switch is able to monitor the status of connected PoE devices and reboots the device when problem occurs.

### Up to 90W Power Output per Blue Port

This switch allows blue port support for IEEE802.3af, IEEE802.3at, and IEEE802.3bt standards. It has a maximum power output of 90 W per port, making the switch suitable for devices with high power consumption rates.

# Specifications

## Hardware

PoE Ports	24 x 10/100/1000 Mbps PoE/PoE+/PoE++
Uplink Ports	2 x 100/1000 Mbps SFP 2 x 10/100/1000 Mbps RJ-45
PoE Standards	IEEE802.3af, IEEE802.3at (PoE+), IEEE802.3bt (PoE++)
Network Standards	IEEE802.3, IEEE802.3u, IEEE802.3x, IEEE802.3ab, IEEE802.3z
PoE Ports Power	Ports 1 to 2: ≤ 90 W (PoE++) Ports 3 to 24: ≤ 30 W (PoE+)
Total Power Budget	375 W
PoE Pin Assignment	1, 2, 4, 5, (V+), 3, 6, 7, 8 (V-)

## Performance

Switching Capacity	56 Gbps
Packet Forwarding Rate	42 Mpps
Packet Buffer Size	4.1 Mbit
MAC Table Size	8,000
MTBF	67.8 Years

## Features

Layer	2
Port Configuration	Port Rate Configuration, Flow Control, and Port Enabling
PoE Watchdog	PoE ports automatically detect and restart unresponsive cameras.
Long Distance Transmission	Up to 820 ft (250 m) at 10 Mbps on PoE Ports
VLAN	Port-Based
VLAN Number	32
IEEE 802.3x Flow Control	Supported
Storm Control	Unknown Unicast, Multicast, and Broadcast
Port Mirroring	Supported
Port Isolation	Supported
LLDP	Supported
DHCP Function	Client

## Electrical

Power Supply	100-240 VDC, 47-63 Hz, Max, 7 A, Internal Power Supply
Power Consumption	Idle: 12.5 W Total: 400 W
Surge Protection	Power Port: 4 kV/2 kV Telecom Port: 8 kV

## Construction

Net Weight	2.7 kg (5.9 lb)
Gross Weight	3.3 kg (7.2 lb)
Operating Temperature	-10 to 55 °C (14 to 131 °F) 5 to 95% (RH), Non-Condensing
Storage Temperature	-40 to 70 °C (-40 to 158 °F) 5 to 95% (RH), Non-Condensing
Product Dimensions (L x W x H)	440.0 mm x 220.0 mm x 44.0 mm (17.3 in. x 8.7 in. x 1.7 in.)
Material	Metal

## Certifications and Compliance

Certifications	FCC Part 15 Subpart B
----------------	-----------------------

## Transmission Performance

Switch power supply voltage 53V.  
CAT5E/CAT6. Max. DC resistance < 10Ω/100m

### PoE++ (90 W)

Cable (ft)	Load Capacity (W)	Bandwidth (Mbps)
328	71.3	1000
492	62	10
656	51	10
820	40	10

### PoE+ (30 W)

Cable (ft)	Load Capacity (W)	Bandwidth (Mbps)
328	25.5	1000
492	25.5	10
656	25.5	10
820	25.5	10

Note: Data from this table was collected by Luminy Systems Corporation test lab and is for reference only. The actual transmission distance may vary due to power consumption of connected devices or the cable type and status.

## Dimensional Drawings

