



Siemens Low Voltage Residential Generators Standby power (Generators) -
Generators: Accessories are Residential Enclosures Standby power (Generators).
Sub Brand: Standby Power Systems Type: Manual Transfer Interlock Kit
Application: For use on load centers or meter combinations that will accept 2-pole
circuit breakers opposite one another Standard: UL/NEMA 1/3R Amperage Rating:
225A Mounting: Flush or Surface Length: 3.6 Width: 5.1 Height: 12.9

General technical data	
fastening method	Flush or Surface
product function note	
suitability for operation	For use on load centers or meter combinations that will accept 2-pole circuit breakers opposite one another
Electricity	
operational current at AC rated value	225 A
Model	
product brand name	Siemens
product sub brand name	Standby Power Systems
product type designation	Manual Transfer Interlock Kit
Mechanical Design	
depth [in]	3.6 in
height [in]	12.9 in
width [in]	5.1 in
General product approval	
certificate of suitability	UL/NEMA 1/3R

last modified:

10/22/2025 

