

## OPT-X™ 500i SDX Rack-Mount Enclosures and Panels 1RU, 2RU, and 3RU

### APPLICATION

OPT-X 500i SDX Rack-Mount Enclosures and Panels allow for inter-connect or cross-connect between backbone cable and active equipment while using minimum rack space in a frame or cabinet setting. The features and design allow for easy field termination of connectors, splicing, or installation of pre-terminated plug-n-play solutions. These economical enclosures and panels are ideal for small-enterprise applications.



5R1UL-F03



5R2UL-F06



5R3UL-F12



5R1UE-OPX



5R3UE-OPX

### STANDARDS COMPLIANCE

- ANSI/TIA-568-C.3

### COUNTRY OF ORIGIN

Mexico (for 5RxUL)  
USA (for 5RxUE)

### SPECIFICATION

Fiber enclosures shall have a flush-mount bulkhead and shall be available in 1RU, 2RU, and 3RU versions to accommodate termination and splicing of fiber. Fiber panels shall have a flush-mount bulkhead and shall be available in 1RU and 3RU versions to accommodate termination of fiber. Adapter bulkhead shall accept SC, LC, ST, MTP®, and QUICKPORT™ adapter plates and plug-n-play MTP modules/cassettes. Fiber cable management for routing, storage, and protection shall be inclusive of patch cords, tight-buffer fiber, and backbone cables. Enclosures and panels shall be constructed of 16-gauge steel with a powder-coated black finish and be mountable in a 19-inch rack or cabinet frame.

### FEATURES

- Flush-mount adapter bulkhead makes moves, adds, and changes easy
- Stackable fiber rings simplify cable routing and organization
- One-piece removable cover on enclosure allows for complete accessibility to the back of the enclosure and protect fibers
- Constructed of 16-gauge steel, powder-coated black
- Add-on patch cord cable management tray (sold separately) shares existing rack unit with the mounted enclosure
- Convert to HDX cassettes or adapter plates using conversion bracket (sold separately)

### DESIGN CONSIDERATIONS

- Enclosures and panels are sold empty (unloaded)
- Accepts SDX adapter plates, MTP cassettes, or splice modules
- Optional cable strain-relief clamp kits available for installation on side of enclosure or on rack post
- 19-inch enclosure/cabinet rack mount
- Enclosure is capable of storing up to three meters of 900 μm tight-buffered fiber per adapter opening
- Accessory kit for enclosure consists of cable ties, mounting ear screws, and ID label
- Accessory kit for panel consists of mounting screws

### MECHANICAL SPECIFICATIONS










Dimensions: See page two

Materials: Constructed of 16-gauge steel, powder-coated black

Temperature (Installation): -10 °C to +60 °C

Temperature (Operating): -10 °C to +60 °C

**PRODUCT SPECIFICATIONS**  
**5RxUL-Fxx, 5RxUE-OPX**



**PRODUCT SPECIFICATIONS**  
**5RxUL-Fxx, 5RxUE-OPX**



**5RxUL-Fxx, 5RxUE-OPX**

**OPT-X™ 500i SDX RACK-MOUNT ENCLOSURES AND PANELS**

DESCRIPTION	PART NO.
1RU Enclosure, Empty	5R1UL-F03
2RU Enclosure, Empty	5R2UL-F06
3RU Enclosure, Empty	5R3UL-F12
1RU Panel, Empty	5R1UE-OPX
3RU Panel, Empty	5R3UE-OPX

**ACCESSORIES**

DESCRIPTION	PART NO.
Universal OPT-X Clamp Kit (for enclosure)	5RCMP-KIT
Universal OPT-X Clamp Kit (for rack post)	5RCMR-KIT
Fiber Cable Management ¼ Ring Kit (bag of four)	5R100-14R
Universal Patch Cord Management, 0RU	5RCMT-VFG
Universal Patch Cord Management Tray, 1RU	5R1UX-CMT
Universal Patch Cord Management Tray, 2/3RU	5R2UX-CMT
HDX to SDX Adapter Bracket	HDXAD-ACC

**DENSITY**

Rack Unit(s)	Fibers (using LC)	SDX Adapter Plates, MTP® Cassettes, or Splice Modules	Splice trays
1RU Enclosure	72	Up to 3 (horizontal orientation)	Up to 3
2RU Enclosure	144	Up to 6 (horizontal orientation)	Up to 6
3RU Enclosure	288	Up to 12 (vertical orientation)	Up to 12
1RU Panel	72	Up to 3 (horizontal orientation)	n/a
3RU Panel	288	Up to 12 (vertical orientation)	n/a

For further support information, visit [leviton.com/ns/support](http://leviton.com/ns/support)

Page 3 of 3

**USA**  
 Network Solutions Headquarters  
 +1 (800) 722 2082  
[infoUSA@leviton.com](mailto:infoUSA@leviton.com)

Leviton Berk-Tek Cable: +1 (800) 237 5835  
[berktek.info@leviton.com](mailto:berktek.info@leviton.com)

**Asia Pacific**  
 +852 3620 2602  
[infoAPAC@leviton.com](mailto:infoAPAC@leviton.com)

**Canada**  
 +1 (800) 461 2002  
[infoCanada@leviton.com](mailto:infoCanada@leviton.com)

**Europe**  
 +44 (0) 1592 772124  
[infoEurope@leviton.com](mailto:infoEurope@leviton.com)

**Latin America**  
 MX: +52 (55) 2128 6286  
 LATAM: +52 (55) 2333 5963  
[infoLATAM@leviton.com](mailto:infoLATAM@leviton.com)

**Middle East & Africa**  
 +971 (4) 247 9800  
[infoMEA@leviton.com](mailto:infoMEA@leviton.com)

NETWORK SOLUTIONS PRODUCTS ARE AVAILABLE WORLDWIDE IN OVER 100 COUNTRIES. VISIT US ONLINE AT [LEVITON.COM/NS](http://LEVITON.COM/NS) TO LEARN MORE.