


Nylon Insulated Support Sleeve

Nylon insulated colour coded barrel styles offer the ultimate in high-performance terminal design and construction. Tin-plated brass sleeve strengthens barrel and secures wire to protect against stress and high vibration. Permanently-attached colour-coded Nylon insulating sleeve extends beyond the metal support sleeve. Funnel ferrule wire entrance into electrical barrel eliminates wire strand 'hang-up', increases crimping rates and wire termination reliability. Operating Temperature Range: continuous duty from -67°F to 221°F (-55°C to 105°C).



Copper Solid and Stranded Wire Only









16-14 WIRE RANGE

.032 Stock

600 Volts


Stud Size Part Number



Stud Size Part Number



Terminals are NOT Actual Size See Sizing Chart on B-38, B-39



DIMENSIONAL CHART		
Part Number	W	L
B8B		1.058"
BS6B10	0.299"	0.880"
BS6B6	0.299"	0.897"
BS6B6S	0.246"	0.885"
BS6B8	0.298"	0.897"
R6B10	0.342"	1.033"
R6B38	0.530"	1.201"
R6B56S	0.464"	1.165"
R6B6	0.313"	0.980"
R6B6S	0.255"	0.935"
R6B8	0.313"	0.983"
R6B8S	0.252"	0.886"

Terminals accept .170" Max. Wire Ins. Dia.; Splices - .150"

Add suffix "M" for 1000 pack

Add suffix "P" for Pro Pack (Quantities vary by Part #)

Approved installation tool: See tool chart pages E-2,3,4

Economy installation tools: RAT-NYL, 453, HTS1000

See pages E-2 to E-4 for installation tools.