

## FEATURES & SPECIFICATIONS

**INTENDED USE** — For use with housings L7X, L7XR, LC6, L7XF and L7XFR.

**CONSTRUCTION** — Aluminum one piece reflector.

Polyester powder coat paint.

All finishes have integral flange.

**INSTALLATION** — Socket to trim interface.

Trim retention is achieved by utilizing two side-mounted torsion springs on the trim and two receiving brackets in the can, ensuring a consistently tight fit with the ceiling.

**LISTINGS** — UL Listed to U.S. and Canadian safety standards.

Damp location listed.

**WARRANTY** — 1-year limited warranty. This is the only warranty provided and no other statements in this specification sheet create any warranty of any kind. All other express and implied warranties are disclaimed. Complete warranty terms located at [www.acuitybrands.com/support/warranty/terms-and-conditions](http://www.acuitybrands.com/support/warranty/terms-and-conditions)

**Note:** Actual performance may differ as a result of end-user environment and application. Specifications subject to change without notice.

Catalog Number
Notes
Type

6" Full Reflector Trim

# 7B2

**BAFFLE**

Narrow Flange




### Specifications

Height: 6 (15.2)

Lamp opening: 5-7/8 (14.9)

Diameter: 7-5/8 (19.4)

All dimensions are inches (centimeters) unless otherwise indicated.



### ORDERING INFORMATION

**Example:** 7B2W TOR

7B2		TOR
Series	Finish	Mounting method
7B2	W White baffle MW Matte white	TOR Torsion springs

<b>Accessories:</b> Order as separate catalog number.	
CRT6	6" goof ring, white

Housing Compatibility: Housing and trim ordered separately.			
Application	Source	Maximum wattage	Housing
IC	Incandescent	75 PAR30	L7X, L7XR, LC6
		65 BR30	
	Fluorescent	13DTT	L7XF, L7XFR
		26TRT	

## 7B2 6" Baffle Full Reflector Trim

For BR and PAR reflector lamps, see lamp manufacturer's published raw lamp data for photometrics.