

Electrical sub-base VAVE-L1-1VR8-LP

Part number: 573919

FESTO



 [General operating condition](#)

Data sheet

| Feature | Value |
|----------------------------------|-----------------------------------------------|
| Reverse polarity protection | Bipolar |
| Additional functions | Spark suppression |
| Signal status display | LED |
| Nominal operating voltage DC | 12 V |
| Surge resistance | 0.8 kV |
| Contamination level | 3 |
| Corrosion resistance class (CRC) | 2 - Moderate corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B2-L |
| Degree of protection | IP65 |
| Ambient temperature | -5 °C ... 60 °C |
| Mounting position | Any |
| Max. tightening torque | 0.27 Nm |
| Product weight | 3.2 g |
| Electrical connection | 3-pin/2-pin M8 / - Plug/socket |
| Protective earth connection | Not available |
| Type of mounting | On air solenoid valve with self-tapping screw |
| Housing colour | Black |
| Note on materials | RoHS-compliant |
| Cover material | PA |
| Seals material | EPDM |
| Housing material | PA |
| Material of screws | Tempered steel |