

## BAND SAW BLADES

### Choosing the right tooth geometry

8/10 Tpi Tooth pitch 2.3/1.8 mm	10 Tpi Tooth pitch 2.5 mm	12/14 Tpi Tooth pitch 1.8/1.4 mm	14 Tpi Tooth pitch 1.8 mm	18 Tpi Tooth pitch 1.4 mm	25 Tpi Tooth pitch 1 mm
FOR CUTTING STOCK 5 to 13 mm	FOR CUTTING STOCK 8 to 13 mm	FOR CUTTING STOCK 4 to 8 mm	FOR CUTTING STOCK 5 to 8 mm	FOR CUTTING STOCK 4 to 5 mm	FOR CUTTING STOCK < 4 mm

## EXTREME METAL BAND SAW BLADES

### OVERVIEW

Our Extreme Metal Band Saw Blades deliver exactly what you need for daily job site use – More Cuts and Less Blade Changes. An aggressive variable pitched tooth design gives you the versatility to cut more metal thickness with one band saw blade. The portable band saw blade's versatility pairs with 3X longer life in stainless steel. Each blade gives you more cuts, resulting in fewer blade changes. The band saw blade also gives fast, clean cuts in common materials, delivering the performance you are looking for in a single blade.

### FEATURES

- More cuts. Less blade changes.
- 3X Life in Stainless Steel and other extreme metals.
- 2X Faster in Thin Metals
- 25% More Cuts Per Charge
- Variable TPI for Versatility in All Metal Thickness
- Optimized Tooth Design for clean cuts
- Made in the USA with global materials
- Aggressive tooth design for 2X Faster cuts in Thick Metals
- Fastest cutting blade in thick, hard metals.
- Cuts More Materials
- One blade for all metal thicknesses
- Variable TPI, Cuts More Materials



### EXTREME METAL BAND SAW BLADES

	44-7/8"			35-3/8"			30-9/16"			27"
TPI	3 Pack	25 Pack	100 Pack	3 Pack	25 Pack	100 Pack	3 Pack	25 Pack	100 Pack	3 Pack
8/10	48-39-0610	48-39-0605	48-39-0603	48-39-0609	48-39-0606	48-39-0653	48-39-0630	48-39-0635	48-39-0637	–
12/14	48-39-0611	48-39-0615	48-39-0613	48-39-0619	48-39-0616	48-39-0663	48-39-0631	48-39-0636	48-39-0639	48-39-0711


## STANDARD BAND SAW BLADES

### OVERVIEW

Our Band Saw Blades are designed to maximize the performance of any portable band saw. The portable bandsaw blades give you long tooth life and exceptional durability in metal-cutting applications, including strut, conduit, angle iron, copper tube, threaded rod, and pipe. Tooth form, pitch, and set have been designed to provide you with straight, accurate cuts across a broad range of materials. Matrix II high-speed steel extends the life of the bandsaw blade in hard materials. This MILWAUKEE Bandsaw Blade pack contains 100 blades for portable compact band saws.

### FEATURES

- High Speed Steel Teeth For Maximum Durability
- Alloy Backing Steel for Extended Blade Life
- Precision Formed Teeth for Fast, Clean Cuts



### STANDARD BAND SAW BLADES

	44-7/8"			35-3/8"			27"
TPI	1 Pack	3 Pack	100 Pack	1 Pack	3 Pack	100 Pack	3 Pack
10	48-39-0500	48-39-0501	48-39-0540	48-39-0508	48-39-0509	48-39-0546	–
10/14	48-39-0550	48-39-0551	48-39-0541	–	–	–	–
14	48-39-0510	48-39-0511	48-39-0542	48-39-0518	48-39-0519	48-39-0547	–
14/18	48-39-0560	48-39-0561	48-39-0543	–	–	–	–
18	48-39-0520	48-39-0521	48-39-0544	48-39-0528	48-39-0529	48-39-0548	48-39-0572
24	48-39-0530	48-39-0531	48-39-0545	48-39-0538	48-39-0539	48-39-0549	–