

GNAH292N, Mechanical Grounding Terminal, Cable to Flat, NEMA-drilled pad, IEEE 837

By Burndy
Catalog # [GNAH292N](#)



Cast copper alloy grounding terminal for equipment or structure grounding type applications. Assembled with DURIMUM™ (silicon bronze) hardware. Qualified to IEEE 837-2014

Features

- IEEE 837-2014 Qualified
- Third-party laboratory test results available
- UL467
- High Copper Alloy Cast Body with Silicon Bronze Hardware
- Parallel or 90° Copper Cable Connection
- Rated for Direct Burial in earth or concrete
- Installation Torque: 480 IN-LB

Application

Mechanical cast copper alloy grounding terminal

General

| | |
|--|-------------------|
| Bolt Installation Torque (Recommended) | 480 in-lbs |
| Catalog Number | GNAH292N |
| Material | Cast Copper Alloy |

UPC 621945659650

Certifications And Compliance

Buy America(n) Qualified Industry Standard(s)
Contact Manufacturer

- UL467
- IEEE 837 2014 Qualified

Product Assets

[Catalogs - Burndy Grounding Catalog](#)
[Catalogs - BURNDY Master Catalog - Section E2 - Mechanical Grounding](#)
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Literature - IEEE 837-2104 Qualified Mechanical Grounding Connectors](#)
[Sales Drawings - 50121402](#)
[Specifications - GNAH292N](#)