

OS160LED

OUTDOOR SECURITY SOLUTIONS FOR RESIDENTIAL APPLICATION



NAME:	
TYPE:	
DATE:	
NOTES:	

SPECIFICATIONS

LIGHT UNIT:	<p>Rugged cast-aluminum, corrosion-resistant housing with dark bronze or white powder paint for lasting durability.</p> <p>LED lamp heads are thermally isolated from the driver that is located in the rear housing, promoting a long service life.</p> <p>Adjustable Photocell Sensitivity</p> <p>Twin head lenses are sealed to keep out moisture, dirt and bugs.</p> <p>LEDs maintain 70% of light output at 50,000 hours of service life.</p>
INSTALLATION:	<p>Crossbar and hardware provided.</p> <p>Wet location listed for mounting 4 feet above ground.</p> <p>Tool-less adjustable heads allow for precise aiming.</p> <p>Dual mount system: Can be mounted on walls or soffits.</p>
ELECTRICAL:	<p>Energy efficient LED provides 2400 lumens, consumes 23W utilizing 120V 60Hz driver.</p> <p>Selectable Color Temperature, choice of 3000K or 4000K</p> <p>Rated for outdoor installations, -40°C minimum ambient.</p> <p>LISTINGS</p> <p>UL/cUL listed Listed to U.S. and Canadian safety standards for wet locations.</p>

OPERATING TEMPERATURE:	-40°C + 40°C
CRI:	70+
LUMEN OUTPUT:	2400LM
WATTS:	23W
LED LIFE:	50,000 hours
WARRANTY:	5 years
VOLTAGE:	120V


APPLICATIONS

The high performance LED oval twin-head security light offers security and general lighting for outdoor residential and commercial applications. Long lasting, energy saving illumination ideal for yards, driveways, walkways, lots and loading areas.

OS160LED

OUTDOOR SECURITY SOLUTIONS FOR RESIDENTIAL APPLICATION

DIMENSIONS



RATINGS



ORDERING GUIDE

OS160LED SERIES

Series	Finish
OS160LEDPC-2HO	DB Dark Bronze WH White

Notes: Configure product using **BOLD** options: Ex: **OS160LEDPC-2HO-WH**