

Project: _____

Type: _____

Drawn by: _____ Catalogue #: _____

Date: _____

Individual Spec Sheet

LPDL™ ECO CHOICE

LED LOW PROFILE DOWNLIGHT

ORDERING INFORMATION

Order code: 70556
Model number: LPDL4R-9A-5CBK-ECO/CHOICE
UPC: 069549035614
Case quantity: 50

PHYSICAL DATA

Size in (cm): 4 3/4 x 1 1/4 (12 x 1.8)
Shape: Round
Finish: Black
Lens Type: Frosted polycarbonate
Mounting: Recessed

PERFORMANCE DATA

Watts (W): 9
Volts (V AC): 120
Color temperature (K): 2 700/3 000/3 500/4 000/5 000
Lumen output (lm): 750
Efficacy (lm/W): 83.3
CRI: 80+
Life L70 (h): 50 000
Beam angle (°): 110
Environment: Wet location
THD (%): <20
Power factor: >0.9
Cable rating: FT4
Frequency (Hz): 60
Operating temp. range: -30 °C to 45 °C (-22 F° to 113 F°)
Dimmable: Phase cut (ELV / Triac)

¹ Typical colour temperature range: +/- 5 %.

² Lumen values are derived from Energy Star reported data. Initial lumens range: +/- 10 %.

³ Life hours are derived from IESNA LM-80 testing report and projected per IESNA TM-21 extrapolations.

LUMEN SPECIFICATION TABLE

Watts	2 700 K		3 000 K		3 500 K		4 000 K		5 000 K	
(W)	Lumen output (lm)	Efficacy (lm/W)	Lumen output (lm)	Efficacy (lm/W)	Lumen output (lm)	Efficacy (lm/W)	Lumen output (lm)	Efficacy (lm/W)	Lumen output (lm)	Efficacy (lm/W)
9	767	85	809	90	857	95	868	96	829	92

DEFAULT PROGRAMMING

2 700 K



IC rated



quick ship



airtight



ICES 005



LED fixture



wet location


This lighting equipment meets requirements of ICES-005 issue 5 class B for use in residential applications.
 Data is based upon tests performed in a controlled environment.
 Actual performance can vary depending on operating conditions. Specifications are subject to change without notice.

ACCESSORIES (order separately)

Order code	Model number	Type
66821 ¹	ACC/MPLATE/4.25IN/HANG.BARS/STD	Mounting plate with hanger bars
66058	ACC/MPLATE/4.25/ADJ/STD	Adjustable mounting plate
66051	ACC/MPLATE/4.25/SQR/STD	Square mounting plate
66143	ACC/4/VAPOR BARRIER/STD	Vapor barrier extender

¹ Includes brackets and screws.

DIMENSIONS AND WEIGHTS



	4"
Net weight (lbs)	0.53

Qty	Description	Price

I accept the specifications of the luminaire configuration mentioned above.

Name: _____
Company: _____
Signature: _____

Date: _____

Data is based upon tests performed in a controlled environment. Actual performance can vary depending on operating conditions. All products are subject to change or may be discontinued any time without notice. Please contact your Stanpro customer service representative to confirm inventory levels at time of order.