





converter control voltage 24 V AC/DC for semiconductor relay/contactor

product brand name	SIRIUS
product designation	converter
product type designation	3RF39
General technical data	
product function	for 3RF31, 3RF32, 3RF33, and 3RF34...-A semiconductor relays / contactors
degree of pollution	3
protection class IP	IP20
protection class IP on the front according to IEC 60529	IP20
shock resistance according to IEC 60068-2-27	15 g / 11 ms
vibration resistance according to IEC 60068-2-6	2 g
reference code according to IEC 81346-2	T
Substance Prohibitance (Date)	03/07/2024
SVHC substance name	Lead monoxide (lead oxide) CAS-No. 1317-36-8 2-methyl-1-(4-methylthiophenyl)-2-morpholinopropan-1-one CAS-No. 71868-10-5 Melamine CAS-No. 108-78-1
Net Weight	0.045 kg
Main circuit	
number of NO contacts for main contacts	0
number of NC contacts for main contacts	0
type of voltage of the operating voltage	AC
relative symmetrical tolerance of the operating frequency	10 %
Control circuit/ Control	
type of voltage	AC/DC
control supply voltage at AC	
• at 50 Hz rated value	20.5 ... 26.5 V
• at 60 Hz rated value	20.5 ... 26.5 V
control supply voltage at DC rated value	18 ... 30 V
supply voltage frequency for auxiliary and control circuit rated value	50 ... 60 Hz
symmetrical line frequency tolerance	5 Hz
control current at AC rated value	25 mA
control current at DC rated value	25 mA
Auxiliary circuit	
number of NC contacts for auxiliary contacts	0
number of NO contacts for auxiliary contacts	0
number of CO contacts for auxiliary contacts	0
Installation/ mounting/ dimensions	
fastening method side-by-side mounting	Yes
fastening method	clip-on

height	83.5 mm				
width	22.5 mm				
depth	38 mm				
Connections/ Terminals					
type of electrical connection for auxiliary and control circuit	screw-type terminals				
type of connectable conductor cross-sections • for auxiliary and control contacts — solid — finely stranded with core end processing — finely stranded without core end processing • for AWG cables for auxiliary and control contacts	1x (0.5 ... 2.5 mm²), 2x (0.5 ... 1 mm²) 1x (0.5 ... 2.5 mm²), 2x (0.5 ... 1 mm²) 1x (0.5 ... 2.5 mm²), 2x (0.5 ... 1 mm²) 1x (20 ... 12)				
tightening torque for auxiliary and control contacts with screw-type terminals	0.5 ... 0.6 N·m				
tightening torque [lbf·in] for auxiliary and control contacts with screw-type terminals	4.5 ... 5.3 lbf·in				
design of the thread of the connection screw of the auxiliary and control contacts	M3				
stripped length of the cable for auxiliary and control contacts	7 mm				
Electrical Safety					
touch protection on the front according to IEC 60529	finger-safe, for vertical contact from the front				
Ambient conditions					
installation altitude at height above sea level maximum	1 000 m				
ambient temperature • during operation • during storage	-25 ... +60 °C -55 ... +80 °C				
Electromagnetic compatibility					
conducted interference • due to burst according to IEC 61000-4-4 • due to conductor-earth surge according to IEC 61000-4-5 • due to conductor-conductor surge according to IEC 61000-4-5 • due to high-frequency radiation according to IEC 61000-4-6	2 kV / 5 kHz, behavior criterion 2 2 kV, behavior criterion 2 1 kV, behavior criterion 2 140 dBuV in the frequency range 0.15 ... 80 MHz, behavior criterion 1				
electrostatic discharge according to IEC 61000-4-2	4 kV contact discharging / 8 kV air discharging, behavior criterion 2				
conducted HF interference emissions according to CISPR11	Class A for industrial environment				
field-bound HF interference emission according to CISPR11	Class B for the domestic, business and commercial environments				
Approvals Certificates					
Environment	General Product Approval	other			
Environmental Confirmations		 EG-Konf.	 UL		Confirmation
other					
					
Further information					
Information on the packaging https://support.industry.siemens.com/cs/ww/en/view/109813875					
Information for data generation and storage https://support.industry.siemens.com/cs/ww/en/view/109995012					
Information- and Downloadcenter (Catalogs, Brochures,...) https://www.siemens.com/ic10					
Industry Mall (Online ordering system) https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3RF3900-0EA18					
Cax online generator https://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3RF3900-0EA18					





last modified:

4/4/2026 