



□

Hospital Grade AFCI/GFCI specially designed and tested for rigorous healthcare applications.

Features & Benefits

Separate indicator lights on the Dual-Function AFCI/GFCI Receptacles for AFCI Hospital Grade AFCI/GFCI specially designed and tested for rigorous healthcare applications and GFCI make it easy to distinguish between a trip caused by an arc fault and a ground fault

Separate indicator lights on the Dual-Function AFCI/GFCI Receptacles for AFCI Two back-wire holes per termination add and GFCI make it easy to distinguish between a trip caused by an arc fault and a wiring flexibility, eliminate pigtail and save ground fault box space

High-impact-resistant, thermoplastic construction for superior strength and durability Ground terminal back-wire for fast installation

Two indicator lights, one for GFCI and one for AFCI. Easy to distinguish between trip caused by arc fault and trip caused by ground fault. GFCI indicator light flashes if device fails the self-test, signaling that the AFCI/ GFCI receptacle should be replaced Auto-ground clip assures a positive ground to metal box

Part of the radiant® collection of wiring devices and wall plates FSUL Listed (Federal Specification WC596)

Feed-through protection Patented SafeLock® Protection—if critical components are damaged and ground fault protection is lost, power to the receptacle is disconnected

Prevents line-load miswire—no power to the face or downstream receptacles if wired incorrectly

Specifications

General Info

| | | | |
|-----------------------|----------------------------|-------------|--------------------------------------|
| Product Line | Pass & Seymour | Color | White |
| Finish | Matte | UPC Number | 078500727114 |
| Country Of Origin | China | Material | ABS |
| Number of Receptacles | 2 | Outlet Type | AFCI, GFCI, Tamper-Resistant |
| Application Sector | Commercial, Hospital Grade | Type | AFCI, Duplex, GFCI, Tamper-Resistant |

Additional Information

| | |
|----------------|-----|
| RoHS Compliant | Yes |
|----------------|-----|

Technical Information

| | | | |
|---------------------|-----|-----------------|---|
| Is Tamper-Resistant | Yes | Number of Gangs | 1 |
|---------------------|-----|-----------------|---|

| | | | |
|----------|------|----------------------|----|
| Amperage | 20 A | Is Weather Resistant | No |
|----------|------|----------------------|----|

| | | | |
|----------------|--------|---------------|-----|
| Indoor/Outdoor | Indoor | Mounting Type | Box |
|----------------|--------|---------------|-----|

| | |
|---------|---------|
| Voltage | 125.0 V |
|---------|---------|
