



# BD24N2U BD Type Braid, 24" Undrilled

By Burndy  
Catalog # [BD24N2U](#)

Tinned Copper Braid, Undrilled, Length:24 In,Ampere Rating-190 INDOOR, 225 OUTDOOR.

### Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click here for our Braid Configurator Tool:  
[www.hubbell.com/config/BRAID](http://www.hubbell.com/config/BRAID)

### General

Catalog Number BD24N2U  
UPC 621945485228



### Dimensions

Length 24 in

### Certifications And Compliance

Certification - CSA Approved Yes

### Logistics

Carton Quantity 5  
Minimum Pack Quantity 1  
Pallet Quantity 450

### Product Assets

[Catalogs - Burndy Grounding Catalog](#)  
[Catalogs - BURNDY Master Catalog - Section E2 - Mechanical Grounding](#)  
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Customer Notices - Prop 65 Notice](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Sales Drawings - 50078953](#)  
[Specifications - BD24N2U](#)



A Hubbell brand