



- FINGER GUARDS FOR TERMINAL BLOCKS AND FUSING OPTIONAL
- OPTIONAL FUSE CLIPS WILL ADD 0.35"[9mm] TO HEIGHT
- OPTIONAL FUSE CLIPS WITH FINGER GUARDS WILL ADD 0.48"[12mm] TO HEIGHT
- OPTIONAL FUSE BLOCK WILL ADD 1.3"[33mm] TO HEIGHT
- OPTIONAL FUSE BLOCK WITH FINGER GUARD WILL ADD 1.5"[38mm] TO HEIGHT
- TOLERANCES STD. +/- 0.1" [+/-3mm]
- ALL DIMENSIONS ARE IN INCHES [mm]

H1 0V	H2 480 460 440	H3 600 575 550	hps	H1 H2 H3	252L E50394 PDG12 TYPE 3AH	LISTED	LR3902 TYPE 3AH	P/N C2G0250ACP 250 VA 60 Hz 130°C CLASS	LV TERMINAL LOCATION 120 240 115 230 110 220 X4 X2 X3 X1 GND
HV TERMINAL LOCATION MADE IN MEXICO SN	LR3902 TYPE 3AH	H1 H2 H3 X4 X2 X3 X1	hps	CONTROL TRANSFORMER P/N C2G0250ACP 250 VA	T2 T1 X4 X2 X3 X1 GND	CE	LR3902 TYPE 3AH		

NOTES:

hammond
POWER SOLUTIONS

TITLE: 1 PHASE GENERAL PURPOSE CONTROL TFX

1	25/09/16	RH	UPDATED EDB	DES: MSARAF
NO.	DATE	BY	REVISION	SCALE: NTS

SHEET 1 OF 1

EDBC2G0250ACP

1.1 jwen 2025/09/22 10:19

THIS DRAWING CONTAINS STRICTLY CONFIDENTIAL INFORMATION BELONGING TO HAMMOND POWER SOLUTIONS AND MUST NOT BE DISTRIBUTED OUTSIDE AUTHORIZED PARTIES.