

RAZORCORE

Recessed LED Downlight

RZR-601

SPECIFICATION SHEET



SPECIFICATIONS



Light Unit

High-quality polycarbonate trim for a refined, lightweight, and durable finish. A steel backplate and heat sink for effective heat dissipation.

Optics

Edge-lit LED technology uses a light-guided plate to distribute light. A polycarbonate lens is used to provide even illumination throughout the installation.

Electrical & Phase Control

Easily connected to a 120V power supply via provided UL recognized driver. Dimming down to 10% with most standard LED dimmers (see list of approved dimmers). Ambient operating temperature: -20°C (-4°F) to +40°C (+104°F). IC, WET Location and AIR-TIGHT rated. Phase Control: TRIAC, Forward and Reverse Phase. Certifications: This product is ETL listed in USA & Canada, certified to UL standard 1598 and CSA standard C22.2 No. 250.0-08.

Junction Box


Galvanneal junction box, with 5CCT color temperature selector switch and knockouts located at the end and 2 sides. Wiring compartment allows for (8) 12 gauge (AWG) or (10) 14 gauge (AWG) insulated conductors. Connection to one (1) downstream unit is permitted within the junction box compartment. The compartment satisfies junction box volume requirements of CSA C22.2 No. 250.0/UL 1598.

Installation

Ideal for shallow ceiling installations with no housing required. Steel spring clip for easy installation and suitable in t-grid and drop ceiling applications.

Selectable color temperature	27K/3K/35K/4K/5K
Lumen output	985 lumens
Beam angle	107°
CRI	90+
Wattage	12 watts
Dimmable	Yes
Cutting hole	6.25" (159mm)
Mounting plate	AMP600-L MPHB425-600
Wire cable	FTI rated
LED life	50,000 hours
Warranty	5 years
Driver voltage	120 V

DIMENSIONS



APPLICATIONS

The Razor Core Series offers a high-quality polycarbonate trim for a refined, lightweight, and durable finish and features five (5) color temperatures: 27K, 3K, 35K, 4K & 5K to select from. The fixtures are IC and AIR-TIGHT rated allowing for installation in almost any location, even directly under a ceiling joist. Whether it is a Remodel or New Construction installation, these units are well suited for indoor / outdoor residential, hospitality, commercial and multifamily applications.

RATINGS & CERTIFICATIONS



ORDERING GUIDE

Series	Color Temperature	CRI	Wattage	Finish
RZR-601	2700K/3000K/3500K/4000K/5000K	90+	12W	WH White

Note: Configure product using **BOLD** options. Ex.: **RZR-601-WH**

ACCESSORIES

**Adjustable mounting plate**

Versatile adjustable mounting plate allows for installation of all models of NDR Lighting recessed lighting products. Refer to our mounting plate compatibility chart to ensure the proper mounting plate is selected.

**Universal mounting plate with adjustable hanger bars**

This multi-size adjustable mounting plate allows for installation of all models of NDR Lighting recessed lighting products. Refer to our mounting plate compatibility chart to ensure the proper mounting plate is selected.

**Vapour barrier**

This vapour barrier unit may be used with all NDR Lighting recessed lighting products. It is designed to prevent air leakage from your living space into the attic, or any insulated spaces.

**Remodel vapour barrier**

The remodel vapour barrier unit may be used with all NDR Lighting remodel housings. It is designed to prevent air leakage from your living space into the attic, or any insulated spaces.

**Razor cables**

These connecting cables are for use with the NDR Lighting Razor Series. These cables allow for greater flexibility in designing custom layout needs.

**Goof rings**

This goof ring is used when the ceiling hole is wider than the retrofit light unit being installed. Refer to our goof ring compatibility chart to ensure the proper goof ring is selected.