



- FINGER GUARDS FOR TERMINAL BLOCKS AND FUSING OPTIONAL
- OPTIONAL FUSE CLIPS WILL ADD 0.35"[9mm] TO HEIGHT
- OPTIONAL FUSE CLIPS WITH FINGER GUARDS WILL ADD 0.48"[12mm] TO HEIGHT
- OPTIONAL FUSE BLOCK WILL ADD 1.3"[33mm] TO HEIGHT
- OPTIONAL FUSE BLOCK WITH FINGER GUARD WILL ADD 1.5"[38mm] TO HEIGHT
- TOLERANCES STD. +/- 0.1" [+/-3mm]
- ALL DIMENSIONS ARE IN INCHES [mm]

H1 H3 H2 H4 110 220 115 230 120 240 HV TERMINAL LOCATION 1 3 2 4 1 3 2 4 LR3902 TYPE 3AH MADE IN MEXICO SN		H1 H3 H2 H4 CONTROL TRANSFORMER P/N C2G0250PR 250 VA T2 T1 X2 X1 GND	252L E50394 PDG12 TYPE 3AH 	LR3902 TYPE 3AH	P/N C2G0250PR 250 VA 50/60 Hz 130°C CLASS 252L E50394 PDG12 TYPE 3AH	LV TERMINAL LOCATION 24 0V 23 22 X2 X1 GND
---	--	---	---	--------------------	---	---

NOTES:



TITLE: 1 PHASE GENERAL PURPOSE CONTROL TFX

1	25/09/16	RH	UPDATED EDB	DES: MSARAF
NO.	DATE	BY	REVISION	SCALE: NTS

SHEET 1 OF 1

EDBC2G0250PR

1.1 jwen 2025/09/22 10:27

THIS DRAWING CONTAINS STRICTLY CONFIDENTIAL INFORMATION BELONGING TO HAMMOND POWER SOLUTIONS AND MUST NOT BE DISTRIBUTED OUTSIDE AUTHORIZED PARTIES.