

SPR – PRIMA™

HIGH-END COMPACT BASEBOARD

PRIMA™



ELEGANCE, DISCRETION AND EFFICIENCY

The Prima electric baseboard has a distinctive compact format that adapts to various applications without compromising on performance. Thanks to its safe and innovative housing design with concealed elements, it's easy to clean and maintain. Sleek and elegant, Prima adds a modern touch to any room.

- **COMPACT AND EFFICIENT**
UP TO 25% SHORTER THAN A TRADITIONAL BASEBOARD
- **SAFER HOUSING**
6 MM (1/4 IN.) OPENINGS BLOCK ACCESS TO ELEMENTS
- **IMPACT RESISTANT**
REINFORCED FRONT PANEL
- **FAST AND EASY INSTALLATION**
GUIDE MARKS TO FACILITATE MOUNTING TO WALL
- **EASY TO CLEAN**
TWO-CLICK REMOVABLE FRONT PANEL

COLOURS

- **standard:** white
- **ORORA (optional):** refer to stelpro.com/orora/

FINISH

- epoxy-polyester powdercoat

MANUFACTURING

- 22-gauge annealed galvanized steel housing and 20-gauge one-piece front panel that can support 99.8 kg (220 lbs) at the centre
- full-length thermal protection with automatic reset
- discreet air inlet; air exits from the top for maximum air circulation
- full-length wireway

ELEMENT

- single tubular, stainless steel sheathed element with boxed aluminum fins for improved heat dissipation; the element is securely fastened at its centre, floating in nylon sleeves at each end, eliminating expansion and contraction noises during heat cycles

CONTROL

- wall thermostat (not included) – use of a Stelpro electronic thermostat is strongly recommended
- built-in single pole electronic thermostat that can be installed in the right or left junction box (optional)
- low voltage relay kit and disconnect switch (optional)

INSTALLATION

- surface mounted
- connection compartment at each end
- BX and clamp knockouts for the NMD cables located at each end, at the back and under the unit
- oblong mounting holes at 1-inch intervals (top and bottom) and marks every 8 inches to locate studs

WARRANTY

- five years, *three years on electronic components and lifetime warranty on heating element (for original owner)



ULTRA PRECISE ELECTRONIC THERMOSTAT (OPTIONAL)

IDEAL FOR:

living room, dining room, kitchen, bedroom, office

°STELPRO

Stelpro reserves the right to modify at any time the description, manufacturing, or price of its products. Additionally, Stelpro may apply restocking fees or refuse a refund based on one or more of the following criteria: optional color, custom product, assembly with low-demand options. For the latest product information and prices regarding the products, please visit the website www.stelpro.com.

TECHNICAL SPECIFICATIONS

325 W DENSITY PER LINEAR FOOT*		275 W DENSITY PER LINEAR FOOT*		VOLTAGE	TOTAL LENGTH		WALL LENGTH		WEIGHT	
CODE	WATTS	CODE	WATTS	VOLTS	MM	IN.	MM	IN.	KG	LB
SPR0501W	500	SPRM0371W	375	120	566	22 1/4	556	21 7/8	2.6	5.7
SPR0508W	500	SPRM0378W	375	208	566	22 1/4	556	21 7/8	2.6	5.7
SPR0502W	500/375	SPRM0372W	375/280	240/208	566	22 1/4	556	21 7/8	2.6	5.7
SPR0503W	500	---	---	347	566	22 1/4	556	21 7/8	2.6	5.7
SPR1001W	1000	SPRM0751W	750	120	916	36 1/16	906	35 11/16	3.5	7.7
SPR1008W	1000	SPRM0758W	750	208	916	36 1/16	906	35 11/16	3.5	7.7
SPR1002W	1000/750	SPRM0752W	750/560	240/208	916	36 1/16	906	35 11/16	3.5	7.7
SPR1003W	1000	SPRM0753W	750	347	916	36 1/16	906	35 11/16	3.5	7.7
SPR1501W	1500	SPRM1251W	1250	120	1267	49 7/8	1257	49 1/2	4.4	9.7
SPR1508W	1500	SPRM1258W	1250	208	1267	49 7/8	1257	49 1/2	4.4	9.7
SPR1502W	1500/1125	SPRM1252W	1250/940	240/208	1267	49 7/8	1257	49 1/2	4.4	9.7
SPR1503W	1500	SPRM1253W	1250	347	1267	49 7/8	1257	49 1/2	4.4	9.7
---	---	---	---	120	---	---	---	---	---	---
SPR2008W	2000	SPRM1758W	1750	208	1618	63 11/16	1608	63 5/16	5.3	11.7
SPR2002W	2000/1500	SPRM1752W	1750/1315	240/208	1618	63 11/16	1608	63 5/16	5.3	11.7
SPR2003W	2000	SPRM1753W	1750	347	1618	63 11/16	1608	63 5/16	5.3	11.7

*Densities are averages. --- not available


ACCESSORIES

PRODUCT	DESCRIPTION
SIBTE12C	built-in electronic thermostat – Celsius [120 V-240 V]
SIBTE13C	built-in electronic thermostat – Celsius [277 V-347 V]
SPRE153*	built-in electronic low voltage relay [15 A @ 120 V-347 V]
SPRE153T*	built-in electronic low voltage relay with 24 V transformer [15 A @ 208 V-347 V]
SPRRM120T*	built-in electromechanical relay with 24 V transformer [6000 W @ 120 V]
SPRRM240T*	built-in electromechanical relay with 24 V transformer [6000 W @ 240 V and 5200 W @ 208 V]
SPRRM347T*	built-in electromechanical relay with 24 V transformer [6000 W @ 347 V]
SPRRM347C*	built-in electromechanical relay without 24 V transformer [6000 W @ 120 V-347 V]

Electronic relays can receive a PWM (pulsed width modulation) or all-or-nothing (on/off) signal.

*Factory installation only

TECHNICAL DRAWINGS



A = LOCATION OF BUILT-IN THERMOSTAT (OPTIONAL)



Stelpro reserves the right to modify at any time the description, manufacturing, or price of its products. Additionally, Stelpro may apply restocking fees or refuse a refund based on one or more of the following criteria: optional color, custom product, assembly with low-demand options. For the latest product information and prices regarding the products, please visit the website www.stelpro.com.