

hammond

POWER SOLUTIONS

GUELPH, ONT. BARABOO, WI. COMPTON, CA. MONTERREY, MX



HPS UNIVERSAL™
 DRY TYPE ISOLATION/BUCK-BOOST TRANSFORMER

HV/HT

120X240V

BIL

—

TERM.
BORNES

H1 H3 H2 H4

VOLTS	CURRENT COURANT	% RATED VOLTAGE % TENSION NOMINALE	CONNECTION EACH PHASE CONNEXION PAR PHASE

LV/BT

12/24V

BIL

—

TERM.
BORNES

X4 X2 X3 X1

Cust. Ref.
Réf. du client

Serial No.
No. de série

Part No.
No. de pièce

PHASE

kVA

TYPE

Cooling
Refroidissement

Temp. Rise
Échauffement

Temp. Class
Classe de Temp.

Frequency
Fréquence

Impédance %
@ °C

Encl. Type
Type de boîtier

Wt lbs/kg
Poids

Winding
Enroulement

This transformer can be wired as both an isolation transformer and buck-boost transformer. Refer to wiring instructions for details.

d001073bnsrm



hammond

POWER SOLUTIONS

TITLE: 1 PHASE ENCAPSULATED TRANSFORMER
 NAMEPLATE INFORMATION

				DES: MSARAF
				DATE: 26/03/17
NO.	DATE	BY	REVISION	SCALE: NTS


SHEET 1 OF 2

EDBQC75ERCF


0.10 htpd 2026/06/11 12:59

THIS DRAWING CONTAINS STRICTLY CONFIDENTIAL INFORMATION BELONGING TO HAMMOND POWER SOLUTIONS AND MUST NOT BE DISTRIBUTED OUTSIDE AUTHORIZED PARTIES.

FRONT VIEW



SIDE VIEW



FRONT & BOTTOM PANEL IS HINGED FOR ACCESS TO
TERMINALS, BOTTOM MOUNTING HOLES AND REAR KNOCKOUT.

All Dimensions in inches

ENCLOSURE COLOR : ANSI 61 GREY – OUTDOOR

CUSTOMER NOTES:

- HV TERMINATED AT #18 AWG LEAD WIRE
- LV TERMINATED AT #8 AWG LEAD WIRE



TITLE: 1 PHASE ENCAPSULATED TRANSFORMER

NO.	DATE	BY	REVISION	DES: MSARAF
				DATE: 26/03/17
				SCALE: NTS

SHEET 2 OF 2

EDB0C75ERC