

PRODUCT OVERVIEW

ABBHEMEV

Power outlet with EV-rated receptacle



With the rise of high-powered portable EV chargers, there's an increasing demand for durable, EV-rated receptacles that can deliver continuous, reliable power. The ABBHEMEV receptacle is specifically engineered to meet this need — providing a safe, code-compliant solution for EV charging applications.

Features and benefits

- 50 A power outlet EV-rated receptacle
- NEMA 3R weatherproof construction
- G90 galvanized steel construction for superior corrosion resistance
- Durable polyester powder coat finish resists chipping and fading
- All-in-one construction for factory-assured terminations
- Cover design allows cords to exit while maintaining NEMA 3R integrity
- Rolled edge door for cord protection
- Dead-front construction prevents accidental contact with live parts
- Padlockable door helps prevent unauthorized access


TECHNICAL DATA

Receptacle:	NEMA 14-50R
Type:	1-phase / 3-wire
Grounding:	Yes
Amperage:	50 A
Voltage:	125 / 250 V AC
Temperature rating:	-40°C to 60°C
Wire sizes:	#4, #6 or #8 AWG; #10 AWG for ground only
Grade:	Industrial
Torque:	75 in-lbs
Enclosure type:	NEMA 3R
Certification:	cULus

ORDERING INFORMATION



	Part number
4-pack	ABBHEMEV



ENGINEERED
TO OUTRUN

ABB Inc.
305 Gregson Drive
Cary, NC 27511,
United States

electrification.us.abb.com/residential

We reserve the right to make technical changes or modify the contents of this document without prior notice. With regard to purchase orders, the agreed particulars shall prevail. ABB does not accept any responsibility whatsoever for potential errors or possible lack of information in this document.

We reserve all rights in this document and in the subject matter and illustrations contained therein. Any reproduction, disclosure to third parties or utilization of its contents – in whole or in parts – is forbidden without prior written consent of ABB. Copyright© 2025 ABB
All rights reserved

1TQC255400E0001 12.2025