



GBH26, Mech Ground Conn, Cable to Flat, IEEE 837

By Burndy
Catalog # [GBH26](#)

Mechanical Grounding Connector, One Cable to Tower Leg, Equipment or Structure, #4 AWG SOL - 2/0 AWG STR, 1/2"-13 Hardware, IEEE 837

Features


- IEEE 837-2014 Qualified
- Third-party laboratory test results available
- UL467
- High Copper Alloy Cast Body with Silicon Bronze Hardware
- Parallel or 90° Copper Cable Connection
- Rated for Direct Burial in earth or concrete
- Installation Torque: 480 IN-LB

Application

Ground Connector for Copper Cable to Bar

Specifications

Buy America(n) Qualified	Contact Manufacturer
Industry Standard(s)	• UL467 • IEEE 837 2014 Qualified



Configuration

Connector Type	Grounding
----------------	-----------

Dimensions

Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in

General

UPC	621945711242
Construction Material - Main Material	Copper Alloy Cast Copper Alloy

Product Assets

[Catalog \[English\]](#)