




GNAH292N, Mech Ground Term, Cable to Flat, NEMA pad

By Burndy
Catalog # [GNAH292N](#)



Mechanical Grounding Connector, Cable to Equipment or Structure, #6 AWG SOL - 250 kcmil, 1/2"-13 Hardware with 1.75" NEMA spacing, IEEE 837

Features

- IEEE 837-2014 Qualified
- Third-party laboratory test results available
- UL467
- High Copper Alloy Cast Body with Silicon Bronze Hardware
- Parallel or 90° Copper Cable Connection
- Rated for Direct Burial in earth or concrete
- Installation Torque: 480 IN-LB

Application

Mechanical cast copper alloy grounding terminal

Specifications

- | | |
|----------------------|---|
| Industry Standard(s) | <ul style="list-style-type: none">• UL467• IEEE 837 2014 Qualified |
|----------------------|---|

Dimensions

Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in

Force Related

Bolt Installation Torque (Recommended)	480 in-lbs
--	------------

General

UPC	621945659650
Material	Cast Copper Alloy

Product Assets

[Catalog \[English\]](#)