

Project: _____ Type: _____
 Drawn by: _____ Catalogue #: _____ Date: _____

Individual Spec Sheet

A19

LED LAMPS

5 CCT Selectable

ORDERING INFORMATION

Order Code: 70619
Model Number: A19/8.5W/5CCT/STD
UPC: 069549036055
Case Quantity: 50

PHYSICAL DATA

Base: E26
Type: A19

PERFORMANCE DATA

Watts (W):	8.5	Life L70 (h)³:	25 000
Traditional Equivalent (W):	60	Beam Angle:	240
Volts (V AC):	120	Power Factor:	≥0.7
Color Temperature (K)¹:	2 700/3 000/3 500 4 000/5 000	Frequency (Hz):	60
Lumen Output (lm)²:	800	Input Current (A):	100
Efficacy (lm/W):	94	Operating Temp. Range:	- 40 °C / - 40 °F to 40 °C / 104 °F
CRI:	90	Energy Star:	No
Dimmable:	Yes	Warranty:	3 Years

¹ Typical color temperature range: +/- 5 %.

² Lumen values are derived from photometric testing. Initial lumens range: +/- 10 %.

³ Life hours are derived from IESNA LM-80 testing report and projected per IESNA TM-21 extrapolations.

COMPATIBLE DIMMERS¹

Brand	Model
LUTRON	HCL453P, DVCL-253P, AYCL-253P DVELV-300P, SELV-300P, MACL-153P
COOPER	DAL06P, AAL06, SAL06P3
LEVITON	6674, DSL06-1LZ, DSM10-1LZ, IPE04-1LZ, DDMX1


Dimming performance might be impacted when using the above dimmers with only one lamp
 Full performance achieved when using two or more lamps.

¹ This table shows dimmers that have been tested and have demonstrated proper operation under normal conditions. Each installation being unique, various factors such as load, common neutrals or other electrical products on the circuit can, in certain instances, cause variance in system performance. Read and comply to the dimmer installation instructions. Consult dimming system manufacturer for additional support in operation. Some dimmers may require more than one product for stable operation. Stanpro recommends to use dimmers designed to work with LED products. Older dimmers designed for incandescent products may cause erratic operation.

DEFAULT PROGRAMMING

2 700 K

DIMENSIONS



This lighting equipment meets requirements of ICES-005 issue 5 class B for use in residential applications.
 Data is based upon tests performed in a controlled environment.
 Actual performance can vary depending on operating conditions. Specifications are subject to change without notice.