


SCR – RADIANCE™

COVE HEATER



INNOVATION AT THE HEIGHT OF YOUR EXPECTATIONS

The Radiance cove heater is one of the most efficient heating systems available today. Mounted near the ceiling, the Radiance directs heat downward across the room, without being blocked by furniture and other objects. Radiant heat warms people in the room directly, creating comfortable conditions similar to the sun. The Radiance also warms all inanimate objects in its path; these objects absorb the heat and in turn act as a “heat reserve,” initiating a convection-type flow of heated air that further helps maintain the desired room temperature.

- **15% GREATER ENERGY PERFORMANCE COMPARED TO OTHER RADIANT HEATERS**
- **WALL MOUNTED 2.5 IN. FROM THE CEILING – OUT OF REACH OF CHILDREN AND FREES UP SPACE**
- **IDEAL FOR PEOPLE WITH ALLERGIES**
NO FORCED-AIR MOVEMENT
- **COMPACT AND LIGHTWEIGHT**
IDEAL FOR NEW CONSTRUCTIONS AND RETROFITS

COLOURS

- **standard:** soft white
- **Orora (optional):** anodized aluminum paint and black only (refer to stelpro.com/orora/)

FINISH

- front panel: high temperature, high emissivity paint coating for maximum thermal efficiency
- other parts: hybrid epoxy-polyester powder paint

MANUFACTURING

- aluminum front panel
- 18-gauge steel cabinet and back box
- aluminum end covers
- 24-gauge stainless steel reflector
- full-length wireway
- designed and assembled for reduced noise from the expansion and contraction of metal during heating cycles

ELEMENT

- tubular; stainless steel

CONTROL

- wall thermostat (not included) – the use of an electronic thermostat is strongly recommended
- built-in single pole bimetal thermostat installed in the left or right junction box (optional)

INSTALLATION

- wall mounted at a distance of 2.5 in. or more from the ceiling
- all flammable material must be 6 in. or more from the front of the unit

WARRANTY

- five years

IDEAL FOR:

main heat source for any room, above a window or patio door, living space, daycare center, school, playroom, locker room, spa, rooms with limited space



Stelpro reserves the right to modify at any time the description, manufacturing, or price of its products. Additionally, Stelpro may apply restocking fees or refuse a refund based on one or more of the following criteria: optional color, custom product, assembly with low-demand options. For the latest product information and prices regarding the products, please visit the website www.stelpro.com.

TECHNICAL SPECIFICATIONS

PRODUCT	POWER	VOLTAGE	LENGTH		WEIGHT	
			MM	IN.	KG	LB
CODE	WATTS	VOLTS				
SCR0451SW	450	120	860	34	2.9	6.4
SCR0458SW	450	208	860	34	2.9	6.4
SCR0452SW	450/338	240/208	860	34	2.9	6.4
SCR0453SW	450	347	860	34	2.9	6.4
SCR0601SW	600	120	1190	47	4.0	8.9
SCR0608SW	600	208	1190	47	4.0	8.9
SCR0602SW	600/450	240/208	1190	47	4.0	8.9
SCR0603SW	600	347	1190	47	4.0	8.9
SCR0751SW	750	120	1500	59	5.0	11.1
SCR0758SW	750	208	1500	59	5.0	11.1
SCR0752SW	750/563	240/208	1500	59	5.0	11.1
SCR0753SW	750	347	1500	59	5.0	11.1
SCR0756SW	750	600	1500	59	5.0	11.1
SCR0901SW	900	120	1800	71	5.9	13.0
SCR0908SW	900	208	1800	71	5.9	13.0
SCR0902SW	900/675	240/208	1800	71	5.9	13.0
SCR0903SW	900	347	1800	71	5.9	13.0
SCR0906SW	900	600	1800	71	5.9	13.0
SCR1051SW	1050	120	2110	83	7.1	15.7
SCR1058SW	1050	208	2110	83	7.1	15.7
SCR1052SW	1050/788	240/208	2110	83	7.1	15.7
SCR1053SW	1050	347	2110	83	7.1	15.7
SCR1056SW	1050	600	2110	83	7.1	15.7
SCR1201SW	1200	120	2390	94	8.1	17.8
SCR1208SW	1200	208	2390	94	8.1	17.8
SCR1202SW	1200/900	240/208	2390	94	8.1	17.8
SCR1203SW	1200	347	2390	94	8.1	17.8
SCR1206SW	1200	600	2390	94	8.1	17.8
SCR1508SW	1500	208	2690	106	9.1	20.1
SCR1502SW	1500/1125	240/208	2690	106	9.1	20.1
SCR1503SW	1500	347	2690	106	9.1	20.1
SCR1506SW	1500	600	2690	106	9.1	20.1


Consult the optional colours chart or contact your Stelpro representative for all other colours.
Models also available in 277 V and 480 V.

ACCESSORIES

PRODUCT	DESCRIPTION
SCRSPSW	splice plate kit (for installing two units side by side)
SCRBTRSW*	single pole bimetal thermostat with right side end cover
SCRBTLSW*	single pole bimetal thermostat with left side end cover

* Factory installed

TECHNICAL DRAWINGS



FRONT

SIDE

TOP