



# DIMMER COMPATIBILITY

Project: \_\_\_\_\_

Fixture Type: \_\_\_\_\_

Location: \_\_\_\_\_

Contact/Phone: \_\_\_\_\_

<b>INCANDESCENT AND MAGNETIC LOW VOLTAGE - FORWARD PHASE DIMMING</b>						
<b>Fixture Series</b>	<b>Juno Qualified Dimmers</b>					
	<b>Acuity Brands Model Numbers:</b>	<b>Lutron® Model Numbers:</b>	<b>Leviton® Model Numbers:</b>	<b>Cooper® Model Numbers:</b>	<b>Legrand® Model Numbers:</b>	<b>Belkin® Model Numbers:</b>
Juno 4", 6" and 8" Wafer™ LED Downlight Series WF4 SWW5, WF6 SWW6, WF4 REG SWW5, WF6 REG SWW5, WF8 SWW5, WF4 ADJ SWW5, WF6 ADJ SWW5, WF4 ALO19 SWW5, WF6 ALO20 SWW5, WF4 DREG ALO19, WF6 DREG ALO20, WF4 SQ ALO40 SWW5 and WF6 SQ ALO41 SWW5	SensorSwitch™ WPD-WH	Caséta® PD-6WCL Series  Lutron® Radio RA2® RRD-10ND  Vive Maestro® WIRELESS MRF2S-6ND  Lutron® Radio RA2® RRD-PRO  Maestro® MACL-153MH	IllumaTech™ IPLO6 Series  Leviton® SureSlide IPM06-1LZ			
<b>ELECTRONIC LOW VOLTAGE - REVERSE PHASE DIMMING</b>						
	<b>Juno Qualified Dimmers</b>					
	<b>Acuity Brands Model Numbers:</b>	<b>Lutron® Model Numbers:</b>	<b>Leviton® Model Numbers:</b>	<b>Cooper® Model Numbers:</b>	<b>Legrand® Model Numbers:</b>	<b>Belkin® Model Numbers:</b>
		Diva® DVELV-300P  Caséta® PD-5NE Series  Maestro® MAELV Series  Maestro® MRF2-6ELV Series				

Consult technical services for additional information regarding other dimmer model qualification.



# DIMMER COMPATIBILITY

Project: \_\_\_\_\_

Fixture Type: \_\_\_\_\_

Location: \_\_\_\_\_

Contact/Phone: \_\_\_\_\_

## INCANDESCENT AND MAGNETIC LOW VOLTAGE - FORWARD PHASE DIMMING

### Incandescent and Magnetic Low Voltage - Forward Phase Dimming

- Dimmable with the use of most forward phase dimmers • Dimming range of 100% down to 10% or lower with a minimum load of one fixture and a maximum load of 50% of the dimmer rated load (see example); both dimming range and maximum rated load may vary depending on dimmer model.

Example: Fixture Rating = 10W

Dimmer Rating = 600W

Equivalent Incandescent Load (EIL) Factor = 50% (.5)  
(600/10) X .5 = 30 Fixtures per Dimmer

### Juno Qualified Dimmers

Fixture Series	Acuity Brands Model Numbers:	Lutron® Model Numbers:	Leviton® Model Numbers:	Cooper® Model Numbers:	Legrand® Model Numbers:	Belkin® Model Numbers:
Juno 2" Wafer™ LED Downlight Series WF2 RD and DREG ALO25 SWW5	SensorSwitch™ WPD-WH	Caséta® PD-6WCL Series Lutron® Radio RA2® RRD-10ND Vive Maestro® WIRELESS MRF2S-6ND Lutron® Radio RA2® RRD-PRO	IllumaTech™ IPLO6 Series			

## ELECTRONIC LOW VOLTAGE - REVERSE PHASE DIMMING

### Electronic Low Voltage - Reverse Phase Dimming

- Dimmable with the use of most electronic low voltage dimmers • Electronic low voltage dimmers require a neutral wire in the wall box • Dimming range of 100% down to 10% or lower with a minimum load of one fixture and a maximum load of 75% of the dimmer rated load (see example); both dimming range and maximum rated load may vary depending on dimmer model.

Example: Fixture Rating = 10W

Dimmer Rating = 600W

Equivalent Incandescent Load (EIL)  
Factor = 75% (.75)  
(600/10) X .75 = 45 Fixtures per  
Dimmer

### Juno Qualified Dimmers

Fixture Series	Acuity Brands Model Numbers:	Lutron® Model Numbers:	Leviton® Model Numbers:	Cooper® Model Numbers:	Legrand® Model Numbers:	Belkin® Model Numbers:
Juno 2" Wafer™ LED Downlight Series WF2 RD and DREG ALO25 SWW5		Diva® DVELV-300P Caséta® PD-5NE Series Maestro® MAELV Series Vive Maestro® MRF2S-6ELV Series				

Consult technical services for additional information regarding other dimmer model qualification.

Dimmer compatibility is based on laboratory testing and dimming performance may vary in the field due to a variety of factors. The inclusion of a dimmer on this list is not a guarantee or warranty of compatibility. Dimmers not included on this list do not represent unacceptability, but rather just an indication they have not been evaluated. Refer to dimmer manufacturers for additional information regarding compatibility and performance.

