




- Features:**
- Power supply with TopBoost, PowerBoost and configurable overload behavior
 - Configurable digital signal input and output, optical status indication, function keys
 - Communication interface for configuration and monitoring
 - Optional connection to IO-Link, EtherNet/IP™, Modbus TCP or Modbus RTU
 - Suitable for both parallel and series operation
 - Natural convection cooling when horizontally mounted
 - Pluggable connection technology
 - Electrically isolated output voltage (SELV/PELV) per EN 61010-2-201/UL 61010-2-201
 - Marker slot for WAGO marking cards (WMB) and WAGO marking strips

Technical data		
Input		Input
Phases	1	Mains failure hold-up time
Nominal input voltage $U_{in\,nom}$	1 x 100 ... 240 VAC	≥ 25 ms (230 VAC)
Input voltage range	1 x 90 ... 264 VAC	
Nominal mains frequency range	50 ... 60 Hz	
Input current I_i	≤ 1.2 A (240 VAC; nominal load); ≤ 2.7 A (100 VAC; nominal load)	
Inrush current	≤ 11 A (after 1 ms)	
Power factor correction (PFC)	Active	



Output	
Nominal output voltage $U_{o\,nom}$	24 VDC (SELV)
Output voltage range	24 ... 28 VDC (adjustable)
Default Setting	24 VDC
Nominal output current $I_{o\,nom}$	10 A (24 VDC)
Nominal output power	240 W
Deviation	≤ 1 %
Residual ripple	≤ 70 mV (peak-to-peak)
Current limitation	1.1 x $I_{o\,nom}$ (typ.)
Overload behavior	TopBoost/PowerBoost/Time-limited constant current mode (other overload behaviors can be set)
PowerBoost	15 ADC (5 s)
TopBoost	Up to 600 %

Efficiency/Power Losses	
Power loss P_I	≤ 1 W (standby); ≤ 2.2 W (no load); ≤ 12 W (230 VAC; nominal load)
Efficiency (typ.)	95.2 % (230 VAC; 10 A; 25 °C)

Safety and protection	
Isolation voltage (pri.-sec., AC)	3510 V
Isolation voltage (pri.-PE, AC)	2200 V
Isolation voltage (sec.-PE)	0.5 kVDC
Isolation voltage (sec.-signal)	0.5 kVDC
Protection class	I
Protection type	IP20; per EN 60529
Resistance to reverse feed	≤ 35 VDC
Overvoltage category	III (≤ 2000 m a.s.l.); II (> 2000 m a.s.l.)
Pollution degree	2
Transient suppression (primary)	Yes
Overvoltage protection; secondary	Internal protective circuit ≤ 35 VDC (in the event of a fault)
Short-circuit-protected	Yes
Open-circuit-proof	Yes
Parallel operation	Yes
Series operation	Yes
MTBF	> 1,200,000 h (per IEC 61709)

Connection Data	
Connection 1	
Connection type	Input/output/signaling
Connection technology	CAGE CLAMP®
WAGO connector	WAGO 721 Series
Solid conductor	0.08 ... 2.5 mm² / 28 ... 12 AWG
Fine-stranded conductor	0.08 ... 2.5 mm² / 28 ... 12 AWG
Fine-stranded conductor; with insulated ferrule	0.25 ... 1.5 mm² / 20 ... 16 AWG
Fine-stranded conductor; with uninsulated ferrule	0.25 ... 2.5 mm² / 20 ... 14 AWG
Strip length	8 ... 9 mm / 0.31 ... 0.35 inches

Signaling and Communication	
Signaling	Optical status indication (DC OK; load; warning and error states) Digital signal input and output (DI/DO)
Communications	USB (750-923 Communication Cable) Ethernet/IP™ (2789-9023 Communication Module) IO-Link (2789-9080 Communication Module) Modbus RTU (Communication Module 2789-9015) Modbus TCP (2789-9052 Communication Module)

Circuit Protection	
Internal fuse	T 6.3 A / 250 VAC
Backup fuse (recommended)	16 A (for USA/Canada: 15 A)



Physical data	
Width	50 mm / 1.969 inches
Height	130 mm / 5.118 inches
Depth from upper-edge of DIN-rail	130 mm / 5.118 inches
Note (dimensions)	Height without connector Height with connector: 166 mm

Mechanical data	
Mounting type	DIN-35 rail

Material data	
Fire load	0.338 MJ
Weight	1063.5 g

Environmental requirements	
Ambient temperature (operation)	-25 ... +70 °C (Device starts at -40 °C (type-tested))
Ambient temperature (storage)	-40 ... +85 °C
Relative humidity	5 ... 96 % (no condensation permissible)
Derating	-3 %/K (> 55 °C and U _I < 230 VAC); -3 %/K (> 60 °C and U _I ≥ 230 VAC)
Climatic category	3K3 (per EN 60721)
Operating altitude (max.)	5000 m

Standards and Specifications	
Conformity marking	CE
Standards/specifications	EN 61010-1 EN 61010-2-201 EN 61204-3 UL 61010-1 UL 61010-2-201 SEMI F47 UL 121201 (HazLoc)

Commercial data	
PU (SPU)	1 pcs
Packaging type	Box
Country of origin	IN
GTIN	4066966861204

Product Classification	
UNSPSC	39121004
ETIM 9.0	EC002540
ETIM 10.0	EC002540
ECCN	NO US CLASSIFICATION



Environmental Product Compliance	
RoHS Compliance Status	Compliant, No Exemption

Approvals / Certificates

General approvals			Declarations of conformity and manufacturer's declarations		
 					
Approval	Standard	Certificate Name	Approval	Standard	Certificate Name
EAC GZO Almaty Standart	TP TC 004/2011	EAC CoC 03080	EU-Declaration of Confor- mity WAGO GmbH & Co. KG	-	-
EAC GZO Almaty Standart	TP TC 020/2011	EAC CoC 03081	MFD for SEMI F47 WAGO GmbH & Co. KG	-	-
UL Underwriters Laboratories Inc.	UL 61010-2-201	E255817	UK-Declaration of Confor- mity WAGO GmbH & Co. KG	-	-

Approvals for hazardous areas

		
Approval	Standard	Certificate Name
UL Underwriters Laboratories Inc. (HAZARDOUS LOCA- TIONS)	UL 121201	A-E198726

Downloads

Environmental Product Compliance	
Compliance Search	
Environmental Product Compliance 2787-2146	

Documentation

Manual				Bid Text			
Product Manual Power supply; Pro 2; 1-phase; 24 VDC output voltage; 10 A output current	V 1.2.2 18.02.2022	pdf 8191.26 KB		2787-2146_EUSA	04.07.2019	docx 23.35 KB	
				2787-2146_EUSA		xml 7.91 KB	
				ausschreiben.de 2787-2146			



Instruction Leaflet			
WAGO Pro 2 Power Supplies	V 1.1.0 26.04.2021	pdf 4459.96 KB	

CAD/CAE-Data	
CAD data	CAE data
2D/3D Models 2787-2146	EPLAN Data Portal 2787-2146
	ZUKEN Portal 2787-2146

Runtime Software			
Firmware			
2787-2146, Stromversorgung; Pro 2	V 010513 13.10.2021	zip 1187.33 KB	

1 Compatible Products
1.1 Product Expansions
1.1.1 Communication Module

Item No.: 2789-9023 Communication module; EtherNet/IP; MQTT Pub/Sub; communication capability	Item No.: 2789-9080 Communication module; IO-Link; communication capability	Item No.: 2789-9015 Communication module; Modbus RTU; RJ45; communication capability	Item No.: 2789-9052 Communication module; Modbus TCP; communication capability

1.2 Optional Accessories
1.2.1 Cables and connectors
1.2.1.1 Communication cable

Item No.: 750-923/000-001 Configuration cable; USB connector; Length: 5 m

1.2.3 Marking
1.2.3.1 Marker
Item No.: 2009-115 WMB-Inline; for Smart Printer; 1500 pieces on roll; stretchable 5 - 5.2 mm; plain; snap-on type; white



1.2.3.2 Marker carrier



Item No.: 2789-1233
Marker carrier; for WMB or marking strips;
Length: 33 mm

1.2.3.3 Marking strip



Item No.: 2009-110
Marking strips; for Smart Printer; on reel;
not stretchable; plain; snap-on type; white

1.2.4 Tool

1.2.4.1 Operating tool



Item No.: 210-720
Operating tool; Blade: 3.5 x 0.5 mm; with a
partially insulated shaft; multicoloured



Item No.: 210-721
Operating tool; Blade: 5.5 x 0.8 mm; with a
partially insulated shaft; multicoloured