






Data Sheet | Item Number: 787-3861/400-1000

Electronic circuit breaker; 1-channel; 24 VDC input voltage; 4 A; NEC Class 2; Signal contact

<https://www.wago.com/787-3861/400-1000>



Features:

- Space-saving ECB with one channel
- Reliably and safely trips in the event of an overload and short circuit on the secondary side
- Switch-on capacity < 7,000 μ F
- Enables the use of an economical, standard power supply
- Minimizes wiring via two voltage outputs and maximizes commoning options on both input and output sides (e.g., commoning of the output voltage on 857 and 2857 Series devices)
- Status signal – adjustable as single or group message
- Reset, switch on/off via remote input or local switch
- Prevents power supply overload due to total inrush current thanks to time-delayed switching on during interconnected operation

Notes

Note	The device is designed for use in SELV circuits. Depending on the output current, please use the approved minimum conductor cross-sections.
------	---

Technical data**Input**

Nominal input voltage $U_{i\text{nom}}$	24 VDC
Input voltage range	18 ... 30 VDC

Output

Total number of channels (module)	1
Nominal output voltage $U_{o\text{nom}}$	1 x 24 VDC
Output voltage range	18 ... 30 VDC (U_{e} - voltage drop)
Voltage drop	\leq 320 mV
Nominal output current $I_{o\text{nom}}$	1 x 4 A (fixed setting)
Default Setting	switched off
Trip time	4 ms ... 100 s (load-dependent)
Switch-on capacity	
Switch-on behavior	Time-delayed channel switching (load-dependent, min. 0 ms / max. 500 ms)
Switch-on threshold	DC 20.3 V

Signaling and Communication

Signaling	1 x Status LED (green/yellow/red) 1 x Signal output (18 ... 30 VDC, max. 0.015 A), default setting: tripped
Operation status indicator	Green LED (channel OK) Red LED (channel switched off)
Remote input	1 x Control input (15 ... 30 VDC (active high); 0 ... 5 VDC (active low); max. 0.015 A)

Efficiency/Power Losses

Power loss P_I	\leq 0.4 W (no load)
Efficiency (typ.)	98 %

Circuit Protection

Internal fuse	T 4 A
---------------	-------

Safety and protection

Isolation voltage (connectors – housing)	1.5 kVDC
Protection class	III
Protection type	IP20; per EN 60529
Reverse voltage protection	No
Transient suppression (primary)	Suppressor diode (33 V)
Parallel operation of single channels	Not permitted
Series operation	No
MTBF	1,168,394 h

Insulation coordination (UL)

Overvoltage category	II
Pollution degree	2

Insulation coordination

Overvoltage category	II
Pollution degree	2

Connection Data

Number of jumper slots	8	Connection 1	
		Connection technology	Push-in CAGE CLAMP®
		WAGO connector	WAGO 857 Series
		Solid conductor	0.08 ... 2.5 mm ² / 26 ... 14 AWG
		Fine-stranded conductor	0.34 ... 2.5 mm ² / 22 ... 14 AWG
		Strip length	9 ... 10 mm / 0.35 ... 0.39 inches
		Note (conductor cross-section)	Depending on the output current, use the conductor cross-sections tested and approved by UL: 26 ... 14 AWG (0.5 A); 20 ... 14 AWG (4 A)

Physical data

Width	6 mm / 0.236 inches
Height	94 mm / 3.701 inches
Depth from upper-edge of DIN-rail	97.8 mm / 3.85 inches

Mechanical data

Mounting type	DIN-35 rail
---------------	-------------

Material data

Fire load	0.568 MJ
Weight	53 g

Environmental requirements

Ambient temperature (operation)	-25 ... +70 °C
Ambient temperature (storage)	-40 ... +85 °C
Relative humidity	10 ... 95 % (no condensation permissible)
Derating	No derating
Operating altitude	≤ 2000 m (a.s.l.)

Standards and Specifications

Conformity marking	CE; UKCA
Standards/specifications	EN 61000-6-2 EN 61000-6-3 UL 61010-2-201 DNV UL 1310 (NEC Class 2) UL 2367

Commercial data

PU (SPU)	1 pcs
Packaging type	Bag
Country of origin	IN
Customs tariff number	85362010900

Product Classification

UNSPSC	39121634
ETIM 9.0	EC001440
ETIM 10.0	EC001440
ECCN	NO US CLASSIFICATION

Environmental Product Compliance

CAS-No.	11120-22-2 1303-86-2 1317-36-8 7439-92-1
REACH Candidate List Substance	Diboron trioxide Lead Lead monoxide Lead silicate
RoHS Compliance Status	Compliant,With Exemption
RoHS Exemption	6(c) 7(a) 7(c)-I 7(c)-II
SCIP notification number (Austria)	e069f53f-2f9f-46ed-aa1a-5723c68f4c91
SCIP notification number (Belgium)	4f2ff77b-12e8-4c37-8ddf-95e60225126d
SCIP notification number (Bulgaria)	41aab237-5d95-4bf7-ae81-9f0cf9b1d093
SCIP notification number (Czech Republic)	c63a4fbb-e450-4852-97d7-deb6096dda58
SCIP notification number (Denmark)	1af7f43e-102b-4f0f-bc3a-c6c23ca5d835
SCIP notification number (Finland)	aa23a496-6486-4678-90d9-d67b0c7537f2
SCIP notification number (France)	0505955a-98bc-4a68-8215-f23bbd97ec1e
SCIP notification number (Germany)	01788881-6158-41a2-a31e-b251b0913e84
SCIP notification number (Hungary)	6179d17c-6b3a-4d12-91d4-103173c6ebf6
SCIP notification number (Italy)	0638c04b-e59d-4e1a-82b4-70a31a0f07b2
SCIP notification number (Netherlands)	570cfa5-044e-4504-a250-ba2632d0366b
SCIP notification number (Poland)	f9f45cf5-9aa8-4130-89bb-c3451553b5e9
SCIP notification number (Romania)	145b6244-15b5-421d-995d-aa1d8ec8360e
SCIP notification number (Sweden)	e8b96400-90cc-4684-85aa-79a15ab438d9

Approvals / Certificates

General approvals **Declarations of conformity and manufacturer's declarations**

Approval	Standard	Certificate Name
EAC GZO Almaty Standart	TP TC 020/2011	EAC CoC 03081
UL Underwriters Laboratories Inc. (ORDINARY LOCATIONS)	UL 61010-2-201	UL E175199 Vol.3 Sec.5
UR Underwriters Laboratories Inc.	-	E175199

Approval	Standard	Certificate Name
EU-Declaration of Conformity WAGO GmbH & Co. KG	-	-
UK-Declaration of Conformity WAGO GmbH & Co. KG	-	-

Approvals for marine applications



Approval	Standard	Certificate Name
DNV DNV Germany GmbH	DNV-CG-0339,Aug.2021	TAA00001D1

Approvals for hazardous areas



Approval	Standard	Certificate Name
UL Underwriters Laboratories Inc. (HAZARDOUS LOCA- TIONS)	UL 121201	E198726

Downloads

Environmental Product Compliance

Compliance Search
Environmental Product Compliance 787-3861/400-1000

Documentation

Manual			
Product Manual Elec- tronic circuit breaker	V 1.0.0 25.03.2024	pdf 6743.82 KB	↓

Instruction Leaflet			
Electronic Circuit Brea- ker	V 1.1.1 11.09.2023	pdf 2491.12 KB	↓

CAD/CAE-Data

CAD data	
2D/3D Models 787-3861/400-1000	↓

1 Compatible Products

1.1 Optional Accessories

1.1.1 Jumper

1.1.1.1 Jumper



[Item No.: 859-410/000-006](#)
Jumper; for jumper slot; 10-way; insula-
ted; blue



[Item No.: 859-410](#)
Jumper; for jumper slot; 10-way; insula-
ted; light gray



[Item No.: 859-410/000-005](#)
Jumper; for jumper slot; 10-way; insula-
ted; red



[Item No.: 859-410/000-029](#)
Jumper; for jumper slot; 10-way; insula-
ted; yellow



[Item No.: 859-402/000-006](#)
Jumper; for jumper slot; 2-way; insulated;
blue



[Item No.: 859-402](#)
Jumper; for jumper slot; 2-way; insulated;
light gray



[Item No.: 859-402/000-029](#)
Jumper; for jumper slot; 2-way; insulated;
yellow



[Item No.: 859-403/000-006](#)
Jumper; for jumper slot; 3-way; insulated;
blue



[Item No.: 859-403](#)
Jumper; for jumper slot; 3-way; insulated;
light gray



[Item No.: 859-403/000-005](#)
Jumper; for jumper slot; 3-way; insulated;
red



[Item No.: 859-403/000-029](#)
Jumper; for jumper slot; 3-way; insulated;
yellow



[Item No.: 859-404/000-006](#)
Jumper; for jumper slot; 4-way; insulated;
blue



[Item No.: 859-404](#)
Jumper; for jumper slot; 4-way; insulated;
light gray



[Item No.: 859-404/000-005](#)
Jumper; for jumper slot; 4-way; insulated;
red













[Item No.: 859-404/000-029](#)
Jumper; for jumper slot; 4-way; insulated;
yellow



[Item No.: 859-405/000-006](#)
Jumper; for jumper slot; 5-way; insulated;
blue












1.1.1.1 Jumper


 <p>Item No.: 859-405 Jumper; for jumper slot; 5-way; insulated; light gray</p>	 <p>Item No.: 859-405/000-005 Jumper; for jumper slot; 5-way; insulated; red</p>	 <p>Item No.: 859-405/000-029 Jumper; for jumper slot; 5-way; insulated; yellow</p>	 <p>Item No.: 859-406/000-006 Jumper; for jumper slot; 6-way; insulated; blue</p>
 <p>Item No.: 859-406 Jumper; for jumper slot; 6-way; insulated; light gray</p>	 <p>Item No.: 859-406/000-005 Jumper; for jumper slot; 6-way; insulated; red</p>	 <p>Item No.: 859-406/000-029 Jumper; for jumper slot; 6-way; insulated; yellow</p>	 <p>Item No.: 859-407/000-006 Jumper; for jumper slot; 7-way; insulated; blue</p>
 <p>Item No.: 859-407 Jumper; for jumper slot; 7-way; insulated; light gray</p>	 <p>Item No.: 859-407/000-005 Jumper; for jumper slot; 7-way; insulated; red</p>	 <p>Item No.: 859-407/000-029 Jumper; for jumper slot; 7-way; insulated; yellow</p>	 <p>Item No.: 859-408/000-006 Jumper; for jumper slot; 8-way; insulated; blue</p>
 <p>Item No.: 859-408 Jumper; for jumper slot; 8-way; insulated; light gray</p>	 <p>Item No.: 859-408/000-005 Jumper; for jumper slot; 8-way; insulated; red</p>	 <p>Item No.: 859-408/000-029 Jumper; for jumper slot; 8-way; insulated; yellow</p>	 <p>Item No.: 859-409/000-006 Jumper; for jumper slot; 9-way; insulated; blue</p>
 <p>Item No.: 859-409 Jumper; for jumper slot; 9-way; insulated; light gray</p>	 <p>Item No.: 859-409/000-005 Jumper; for jumper slot; 9-way; insulated; red</p>	 <p>Item No.: 859-409/000-029 Jumper; for jumper slot; 9-way; insulated; yellow</p>	

1.1.2 Marking

1.1.2.1 Marker

 <p>Item No.: 793-5501 WMB marking card; as card; for terminal block width 5 - 17.5 mm; stretchable 5 - 5.2 mm; plain; snap-on type; white</p>	 <p>Item No.: 793-502 WMB marking card; as card; MARKED; 1 ... 10 (10x); not stretchable; Horizontal marking; snap-on type; white</p>	 <p>Item No.: 793-566 WMB marking card; as card; MARKED; 1 ... 50 (2x); not stretchable; Horizontal marking; snap-on type; white</p>	 <p>Item No.: 793-503 WMB marking card; as card; MARKED; 11 ... 20 (10x); not stretchable; Horizontal marking; snap-on type; white</p>
 <p>Item No.: 793-504 WMB marking card; as card; MARKED; 21 ... 30 (10x); not stretchable; Horizontal marking; snap-on type; white</p>	 <p>Item No.: 793-505 WMB marking card; as card; MARKED; 31 ... 40 (10x); not stretchable; Horizontal marking; snap-on type; white</p>	 <p>Item No.: 793-506 WMB marking card; as card; MARKED; 41 ... 50 (10x); not stretchable; Horizontal marking; snap-on type; white</p>	 <p>Item No.: 793-501 WMB marking card; as card; not stretchable; plain; snap-on type; white</p>
 <p>Item No.: 2009-115 WMB-Inline; for Smart Printer; 1500 pieces on roll; stretchable 5 - 5.2 mm; plain; snap-on type; white</p>			

1.1.2.2 Marking strip

 <p>Item No.: 2009-110 Marking strips; for Smart Printer; on reel; not stretchable; plain; snap-on type; white</p>
--

1.1.3 Potential distribution

1.1.3.1 Potential Distribution Module



Item No.: 787-3861/000-1000
Potential distribution module; 1 potential;
with 8 clamping points 0V; Conductor
cross-section up to 2.5 mm²



Item No.: 787-3861/000-2000
Potential distribution module; 1 potential;
with 8 clamping points 24V; Conductor
cross-section up to 2.5 mm²



Item No.: 787-3861/000-3000
Potential distribution module; 2 potentials;
with 4 clamping points each (0V / 24V);
Conductor cross-section up to 2.5 mm²

1.1.4 Tool

1.1.4.1 Operating tool



Item No.: 210-720
Operating tool; Blade: 3.5 x 0.5 mm; with a
partially insulated shaft; multicoloured