


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PART NUMBER	TAB SIZE	WIRE RANGE AWG (mm ²)	COLOR (NOTE 7)	MAX. INSUL.	DIMENSIONS in.[mm]		
					L ± .03 [0,76]	W ± .02 [0,51]	H ± .02 [0,51]
DNF18250FIBX	.250 x .032 [6,3 x 0,8]	22-18 [0,5-1,0]	RED	.210 [5,33]	.93 [23,6]	.35 [8,9]	.22 [5,5]
DNF14250FIBX	.250 x .032 [6,3 x 0,8]	16-14 [1,5-2,5]	BLUE	.240 [6,09]	.93 [23,6]	.35 [8,9]	.22 [5,5]

NOTES:

1. USED FOR:
 - A. 600V MAX VOLTAGE RATING
 - B. TEMPERATURE RATING OF INSULATION: 105°C (221°F)
 - C. STRANDED COPPER WIRE ONLY
2. INSTALLATION TOOL: CT-100B
3. MATERIAL:
 - A. STAMPING-CDA 260 BRASS, TIN PLATED
 - B. HOUSING-TYPE 66 NYLON
4. SEE www.panduit.com FOR PACKAGE QUANTITIES INDICATED BY PART NUMBER SUFFIX
5. DIMENSIONS IN BRACKETS ARE METRIC EQUIVALENT
6. COLORS ARE TRANSLUCENT



REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
04B	9-4-25	JHNU	JHNU	JSUN	C. REMOVED DNF18205FIBX, DNF18206FIBX, DNF14205FIBX, DNF14206FIBX	013848/01
04A	6-4-25	JHNU	JHNU	JSUN	B. REVISED DRAWING NUMBER: N41600BA-DC WAS A41600 A. REVISED TOOL: CT-100B WAS CT-100A	013848/00
04	2.10.14	JHNU	JHNU	RGB	REVISED NOTE 2	A41600
03	08.30.12	JBN	LCA	VMB	REVISED NOTES. UPDATED DRAWING TO CURRENT STANDARDS	A41600
02	2/01	EJS			WIRE RANGE FOR PARTS DNF18250FIBX,205,206 WAS 0,5-1,5 UPDATED NOTE 1-B	

TITLE		FEMALE DISCONNECTS EXPANDED FULLY INSULATED NYLON, #22-14	
CUSTOMER DRAWING			
ITEM REVISION NAME	N41600BA/04		
DATASET FILE NAME	N41600BA_DC/04B		
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]		MATERIAL:	
.x ± .1 [2.54]	.xxx ± .005 [.13]	SEE NOTES	
.xx ± .01 [.25]	ANGLES ± 5°	DRAWING NUMBER:	
THIRD ANGLE PROJECTION		N41600BA-DC	
DRAWN BY	DATE	CHK	SCALE
T SMA	-	LCA	N.T.S.
SHT 1 OF 1		SIZE	
A		A	

D10100DA/12