
DRAWING NO. 10056329


REV.	DATE	DESCRIPTION	ECO	BY	C'K'D.
A	6/2/05	REDRAWN TO CADD .	10952	PL	DB

CATALOG NUMBER	COPPER CONDUCTOR RANGE		H	L	INSTALLATION TOOLING				TIN PLATED CATALOG NUMBER ⟨5⟩
					Y35 HYPRESS™		Y46 HYPRESS™		
	RUN	TAP			DIE NO.	NO. OF CRIMPS	DIE NO.	NO. OF CRIMPS	
CJC2C2	6 SOL. – 2 STR.	6 SOL. – 2 STR.	29.5 / 1.16	19.1 / .75	CSA 22 CU	1	CSA 22 CU WITH PUAP ADAPTOR OR PCSA 22 CU	1	CJC2C2TN
CJC26C2	1 STR. – 2/0 STR.	6 SOL. – 2 STR.	35.8 / 1.41	19.1 / .75	CSA 24 CU	1	CSA 24 CU WITH PUADP ADAPTOR OR PCSA 24 CU	1	CJC26C2TN
CJC26C26	1 STR. – 2/0 STR.	1 STR. – 2/0 STR.	39.1 / 1.54	19.1 / .75	CSA 24 CU	1	CSA 24 CU WITH PUADP ADAPTOR OR PCSA 24 CU	1	CJC26C26TN
CJC29C26	3/0 STR. – 250 kcmil	6 SOL. – 2 STR.	50.0 / 1.97	19.1 / .75	---	1	CSA 28 CU WITH PUADP ADAPTOR OR PCSA 28 CU	1	CJC29C26TN
CJC29C29	3/0 STR. – 250 kcmil	3/0 STR. – 250 kcmil	52.3 / 2.06	21.1 / .83	---	1	CSA 28 CU WITH PUADP ADAPTOR OR PCSA 28 CU	1	CJC29C29TN
CJC34C26	300 kcmil – 500 kcmil	6 SOL. – 2/0 STR.	60.7 / 2.39	22.4 / .88	---	1	PCSA 28 CU	1	CJC34C26TN
CJC34C29	300 kcmil – 500 kcmil	3/0 STR. – 250 kcmil	67.3 / 2.65	22.4 / .88	---	1	PCSA 30 CU	1	CJC34C29TN
CJC34C34	300 kcmil – 500 kcmil	300 kcmil – 500 kcmil	73.9 / 2.91	27.9 / 1.10	---	1	PCSA 30 CU	1	CJC34C34TN

CROSS REFERENCE	
CATALOG NUMBER	ONTARIO HYDRO STOCK CODE
CJC2C2	---
CJC26C2	---
CJC26C26	721–C8904
CJC29C26	721–C8792
CJC29C29	721–C8911
CJC34C26	721–0C8932
CJC34C29	721–C8946
CJC34C34	721–C8925
CJC34C34	721–C8953



TYPICAL LETTERING



NOTES:

1. GROOVE IS FILLED WITH PENETROX™.
2. SUITABLE FOR DIRECT BURIAL IN EARTH OR CONCRETE.
3. CONNECTORS ARE INDIVIDUALLY SEALED IN CLEAR POLYETHYLENE SHEET.
4. FOR USE WITH GALVANIZED ROD WE RECOMMEND THAT THESE CONNECTORS ARE TIN PLATED.
5. FOR ELECTRO–TIN PLATED CONNECTORS ADD SUFFIX "TN" TO THE CATALOG NUMBER.
6. MATERIAL: ETP COPPER.

TO ORDER BURNDY® PRODUCTS CALL

UNITED STATES:
1–800–346–4175 (LONDONDERRY, NH)

CANADA:
1–800–361–6975 (QUEBEC)
1–800–387–6487 (ALL OTHER PROVINCES)

FOR PRODUCT INFO: http://www.burndy.com

TO ORDER BURNDY PRODUCTS CALL 1–800–346–4175
MANCHESTER, NH 03109, USA
FOR PRODUCT INFO = http://www.fciconnect.com

COMPRESSION GROUND TAP CONNECTOR

ITEM NO: N/A

CAT NO: CJC––C–– (TABLE)

SCALE: 1/1		
DRAWN BY: P LAPONIUS	6/1/05	
CHECKER: D BOISVERT	6/6/05	
DSN APPVL: C CHADBOURNE	5/17/05	
MFG APPVL: R PHELPS	5/17/05	
QC APPVL: C ACKERMAN	5/31/05	
MKT APPVL: --	--	
PROD FAM: --		
PROJECT #: --		
DOCUMENT TYPE: Sales		
REL LEVEL: AutoCAD		

BURNDY

SIZE	DRAWING NO	REV
D	10056329	A
	SHEET 1 OF 1	