



ETF24096TD

24V DC 96W Dimmable Mini Electronic Transformer

Project:

Location:

Qty:

Notes:

DESCRIPTION

24V DC 96W Class 2 Mini Electronic Transformer


Constant Voltage Triac / ELV / MLV Dimmable

FEATURES & BENEFITS

- Super Compact - fits in limited spaces
- UL Listed, Class 2, Type HL
- Short Circuit & Over Load Protection
- Hiccup mode, recovers automatically after fault condition is removed

DIMENSIONS

3 1/4" x 1 5/8" x 1"



WIRING DIAGRAM



ORDERING GUIDE


ETF24096TD

WARNING:

Do not exceed ambient temperature range from -40°F (-40°C) to +140°F (+60°C). Please mount in a shaded area or when mounted indoors install in a well-ventilated area. Load to maximum 80%. Failure to follow these instructions could lead to overheating, short life and void the warranty.

SPECIFICATION	
Applications	LED Tape, 24 V DC Ceiling Fixtures
Power	96 W
Input V / Hz	120 V AC / 47-63 Hz
Output V / A	24 V DC ± 1.5 V / 4 A
Type	Constant Voltage Electronic Transformer
Dimmability	Triac / ELV / MLV
Min / Max Load	20% to 80%
THD	THD<20% @ 120 V max load
Efficiency	88% @ 120 V AC
Power Factor	0.94 @ 120 V AC
THD	< 20%
Protection	Short circuit & Overload auto recovery
Approved Location	Dry and Damp Locations
Ambient Conditions	-40°F (-40°C) to +140°F (+60°C), 20-95% RH
Warranty	3 Year
Certification	c UL us Listed, Class 2, Type HL

Load vs Ambient Temp Curve



Lotus LED Lights USA 250 H Street # 301, Blaine WA 98230 tel 360-200-5500 Hainesport NJ, Naples FL, Vancouver WA	www.LotusLEDLights.com mailing addresses warehouses	Lotus LED Lights CANADA 1080 Cliveden Ave # 6, Delta BC V3M 6G6 tel 604-538-3090 Delta BC & Mississauga ON
---	---	---