

PINNACLE

Diffuser kits for Pinnacle Series Tape Light

TL-CKIT5

SPECIFICATIONS SHEET



SPECIFICATIONS

Housing

Mud-in aluminum extruded channels with perforated flange and a smooth silver anodized finish preventing rusting/corrosion and offering a good heat dissipation to keep the LED tape light cool.

Optics

Polycarbonate lens with frosted finish to provide an evenly diffused illumination throughout the installation.

Kit Contents

The diffuser kit is packed to pair perfectly with 1x 16.4ft (5m) reel of NDR Pinnacle Series 24V tape light items.

Each diffuser kit includes (5) packs of:
1x aluminum channel cut to 39.37" (1m)
1x polycarbonate lens cut to 39.37" (1m)
2x plastic end caps (1 end cap sealed and 1 end cap with hole)

Total contents of each diffuser kit:
16.4ft (5m) of aluminum channel
16.4ft (5m) of polycarbonate lens
10 plastic end caps (5x sealed + 5x with wire hole)


Installation

Suited to fit all NDR Pinnacle Series 24V Tape Light models.
TL-CKIT5 will fit:
All 2-PIN Tape Light and Screw Type connectors
All 3-PIN Tape Light and Screw Type connectors
All 6-PIN Tape Light and Snap Type connectors
Ideal for any mud-in installations and suited for any dry or damp location applications.


*TL-CKIT2 and TL-CKIT5 are recommended for installations using the TL200-RGB-24V reels with connector accessories.

Extrusions length	39" (1m)
Extrusions width	2.44" (62mm)
Extrusions height	0.55" (14mm)
Number of extrusions	5 units
Number of caps	5 pairs
Finishes	Silver

FINISHES



DIMENSIONS



ORDERING GUIDE

Series	Finishes
TL-CKIT5	SV Silver

Note: Configure product using **BOLD** options. Ex.: **TL-CKIT5-SV**