RWF | PULSAIR™

WALL FAN HEATER









THE CLASSIC FAN HEATER

You won't find anything better than this efficient, durable and low noise fan heater. The PULSAIR is extremely popular for many reasons. First, it can be recessed or surface mounted with a surface adapter (optional). It can also be mounted vertically or horizontally so that air can flow either up and down or right and left. Finally, the slim-line PULSAIR can be recessed into a wall thickness of 2 in. to 3 in. While it's a winning heating solution for hallways or bathrooms, it can also be installed anywhere in the house, such as the office, or in commercial spaces. Its nichrome element provides instant heat. Available from 500 W to 2000 W, and from 120 V to 347 V, the PULSAIR is recognized and recommended by those in the know.

VERY QUIET FAN HEATER

THE MOST RESISTANT GRILLE ON THE MARKET

INSTANT HEAT NICHROME ELEMENT

MULTIPLE INSTALLATION OPTIONS RECESSED, SURFACE MOUNTED, HORIZONTAL OR VERTICAL

ADAPTS TO MULTIPLE MARKETS AVAILABLE IN: 120 V, 208 V, 240 V AND 347 V

COLOURS

- standard: white, soft white
- ORORA (optional): refer to www.stelpro.com/en-CA/orora

FINISH

• epoxy-polyester powdercoat

MANUFACTURING

- 20-gauge steel cabinet and 18-gauge steel grille
- quiet fan 40 CFM (500 W to 1000 W models) – 75 CFM (1250 W to 2000 W models)
- thermal protection with automatic reset

ELEMENT

• nichrome element produces instant heat

CONTROL

- built-in thermostat (optional)
- wall thermostat (not included) the use of an electronic thermostat is strongly recommended

INSTALLATION

- wall mounted
- recessed (wall must have a depth of 2 3/8 in. minimum)
- surface mounted with surface adapter (optional)
- four installation positions

WARRANTY

· five years

FOUR INSTALLATION OPTIONS









IDEAL FOR:


hallway, bathroom, locker room, office



TECHNICAL SPECIFICATIONS														
WITHOUT CONTROL		BUILT-IN THERMOSTAT		24 V CONTROL		POWER	VOLTAGE	FLOW		ROW	HEAT	HEAT RISE WEIGH		GHT
CODE	PRICE	CODE	PRICE	CODE	PRICE	WATTS	VOLTS	CFM	М	FT.	°C	°F	KG	LB
RWF0501	155.00					500	120	40	2	6'6"	30	54	2.7	6
RWF0508	155.00					500	208	40	2	6'6"	30	54	2.7	6
RWF0502	155.00					500/375	240/208	40	2	6'6"	30	54	2.7	6
RWF0503	196.00	RWF0503T	227.00	RWF0503C24	243.00	500	347	40	2	6'6"	30	54	2.7	6
RWF0751	164.00					750	120	40	2	6'6"	67	121	2.7	6
RWF0758	164.00					750	208	40	2	6'6"	67	121	2.7	6
RWF0752	164.00					750/563	240/208	40	2	6'6"	67	121	2.7	6
RWF0753	205.00	RWF0753T	236.00	RWF0753C24	252.00	750	347	40	2	6'6"	67	121	2.7	6
RWF1001	166.00					1000	120	40	2	6'6"	76	136	2.7	6
RWF1008	166.00					1000	208	40	2	6'6"	76	136	2.7	6
RWF1002	166.00					1000/750	240/208	40	2	6'6"	76	136	2.7	6
RWF1003	207.00	RWF1003T	238.00	RWF1003C24	254.00	1000	347	40	2	6'6"	76	136	2.7	6
RWF1251	175.00					1250	120	75	2.1	6'10"	65	117	2.7	6
RWF1258	175.00					1250	208	75	2.1	6'10"	65	117	2.7	6
RWF1252	175.00					1250/938	240/208	75	2.1	6'10"	65	117	2.7	6
RWF1253	216.00	RWF1253T	247.00	RWF1253C24	263.00	1250	347	75	2.1	6'10"	65	117	2.7	6
RWF1501	178.00					1500	120	75	2.1	6'10"	79	141	2.7	6
RWF1508	178.00					1500	208	75	2.1	6'10"	79	141	2.7	6
RWF1502	178.00					1500/1125	240/208	75	2.1	6'10"	79	141	2.7	6
RWF1503	220.00	RWF1503T	250.00	RWF1503C24	266.00	1500	347	75	2.1	6'10"	79	141	2.7	6
						2000	120	75	2.1	6'10"	111	199	2.7	6
RWF2002	194.00					2000/1500	240/208	75	2.1	6'10"	111	199	2.7	6
RWF2008	194.00					2000	208	75	2.1	6'10"	111	199	2.7	6
RWF2003	235.00	RWF2003T	266.00	RWF2003C24	282.00	2000	347	75	2.1	6'10"	111	199	2.7	6

Add W for white or SW for soft white (consult the optional colours chart or contact your °STELPRO representative for all other colours). Models also available in 277 V. ---- not available

TECHNICAL DRAWINGS



ACCESSORIES							
PRODUCT	DESCRIPTION	PRICE					
RWFT1**	built-in single pole thermostat [120 V-347 V]	29.00					
RWFT2*	built-in double pole thermostat [120 V-347 V]	40.00					
RWFSA*	surface adapter	42.00					

- * Add W for white or SW for soft white.
 * Supplied with a white knob (with a white grille) and a soft white knob (with a soft white grille)

