

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT PART #	MILITARY PART NO. AND CLASS	STUD SIZE		DIMENSIONS in [mm]				
		ENGLISH	METRIC	L ±.08 [2,0]	W ±.01 [0,3]	C ±.02 [0,5]	M ±.06 [1,5]	H ±.01 [0,3]
PN18-4R	---	#4	---	.80 [20,3]	.25 [6,4]	.22 [5,6]	.67 [17,0]	.12 [3,1]
PN18-4RN	MS25036-148 CLASS 1	---	M3	.74 [18,8]	.22 [5,6]	.18 [4,6]	.63 [16,0]	.12 [3,1]
PN18-6R	MS25036-102 CLASS 1	#6	M3,5	.79 [20,1]	.25 [6,4]	.22 [5,6]	.67 [17,0]	.15 [3,8]
PN18-6RN	MS25036-101 CLASS 1	#6	M3,5	.77 [19,6]	.22 [5,6]	.18 [4,6]	.63 [16,0]	.15 [3,8]
PN18-8R	MS25036-149 CLASS 1	#8	M4	.85 [21,6]	.31 [7,9]	.25 [6,4]	.70 [17,8]	.17 [4,3]
PN18-10R	MS25036-103 CLASS 1	#10	--	.87 [22,1]	.31 [7,9]	.25 [6,4]	.70 [17,8]	.20 [5,1]
PN18-14R	MS25036-150 CLASS 1	1/4"	M6	1.05 [26,7]	.45 [11,4]	.38 [9,7]	.80 [20,3]	.27 [6,9]
PN18-56R	MS25036-104 CLASS 1	5/16"	M8	1.04 [26,4]	.46 [11,7]	.38 [9,7]	.84 [21,8]	.33 [8,4]
PN18-38R	MS25036-105 CLASS 1	3/8"	--	1.14 [29,0]	.53 [13,5]	.43 [10,9]	.91 [23,1]	.39 [9,9]


NOTES:

- VISIT OUR ON-LINE CATALOG AT WWW.PANDUIT.COM FOR A LIST OF CURRENT PARTS APPLICABLE FOR USE WITH THIS PRODUCT.
- DIMENSIONS IN () ARE METRIC.
- WEIGHT: .002 TO .004 Lbs. APROX
- PART INCLUDES:
 - STAMPING: .03" [0,8mm] THK COPPER, TIN PLATED
 - HOUSING: NYLON, RED
 - SLEEVE: BRASS, TIN PLATED
- UL LISTED AND CSA CERTIFIED FOR:
 - #22-18 AWG [0,5-1,5 mm²] SOLID OR STRANDED COPPER WIRE.
 - 221°F [105°C] MAX. OPERATING TEMPERATURE.
 - 600 V. MAX. VOLTAGE RATING
- WIRE STRIP LENGTH:

7/32"	+1/32	+0,8
-0	-0	-0

UL APPROVED TOOLS:

CT-100
CT-1550
CT-1551
CT-2500 (CT-2550CH)



LISTED
587H
E52164



CERTIFIED
LR31212

PART NUMBER		SEE TABLE	
TITLE		3PC. NYLON INSULATED 22-18 BARREL, RING TERMINALS	
ITEM REVISION NAME		CUSTOMER DRAWING	
DATASET FILE NAME		N41543BA/15	
MATERIAL		N41543BA-DC r15A	
DRAWING NUMBER		A41543	
THIRD ANGLE PROJECTION		SEE NOTES	
DRAWN BY	DATE	CHK	SCALE
BDK	06-01-15	LA	N/A
SHEET 1 OF 1		A	