




Color: ■ black



This unmanaged industrial ETHERNET switch (852-111) has five Fast ETHERNET ports for easily setting up small- to medium-sized networks. Its slim design paired with a DIN-rail adapter simplifies installation in the control cabinet and provides high vibration and shock resistance. Additionally, automatic transmission rate detection (auto-negotiation) and automatic identification of the transmit and receive lines (Auto MDI-X) allow simple plug-and-play operation, saving time and money during commissioning.

Features:

- 5 ETHERNET ports 10/100 Mbit/s Autonegotiation
- Front-panel diagnostic LEDs
- Supports Auto-MDI/MDI-X functions
- Full/half-duplex transfer modes for each port
- Store-and-forward switching method
- Integrated address look-up table, supports 2000 absolute MAC addresses
- Overvoltage protection
- Data flow control, per IEEE 802.3x Flow Control, in full-duplex mode
- DIN-35 rail mounting

Technical data

Switching mode	Store-and-forward; non-blocking
Number of 100 Mbps ports	5
Communication standards	IEEE 802.3 10BASE-T IEEE 802.3u 100BASE-TX IEEE 802.3x Flow Control
MAC table (size)	2000 addresses
Jumbo frame size	1536 bytes
Supply voltage	18 ... 30 VDC
Power consumption (max.)	3 W
Current consumption (max.)	150 mA
ESD (contact/air discharge)	4 kV / 8 kV
Transmission rate	Copper cable: 10/100 Mbit/s
Transmission medium (communication/fieldbus)	Copper cable: Cat. 5 or higher, 100 m maximum cable length
Topology	Star
Indicators	Device: LED (PWR) green: Power supply; per port: LED (100, LNK/ACT) green: Status 100 Mbps, LNK/ACT port 1 ... 5

Connection Data

Connection technology: communication/fieldbus	Copper cable: 5 x RJ-45
Connection technology: supply	1 x Built-in male connector: 231-433/001-000; included female connector (MCS Connectors): 231-103/026-000

Physical data

Width	23.4 mm / 0.921 inches
Height	109.2 mm / 4.299 inches
Depth	81 mm / 3.189 inches
Depth from upper-edge of DIN-rail	73.8 mm / 2.906 inches

Mechanical data

Weight	302 g
Color	black
Housing material	Sheet steel

Environmental requirements

Ambient temperature (operation)	-40 ... +70 °C (UL max. +60 °C; -25 ... +70 °C (DNV GL) (see temperature class D))
Ambient temperature (storage)	-40 ... +80 °C
Protection type	IP30
Note on protection type	Use per UL 61010: Indoor
Pollution degree	2 per UL 61010
Relative humidity (without condensation)	95 %
Mounting type	DIN-35 rail
Mounting type	Wall mounting (horizontal or vertical); Dimensions (W x H x D) for wall mounting: 97 x 109.2 x 23.4 mm
Mounting (note)	Standard Compass Safe Distance 0.3 Degree deflection: 1000 mm; Steering, Standby, Emergency Compass Safe Distance 1.0 Degree deflection: 650 mm
Vibration resistance	Per IEC 60068-2-6
Shock resistance	per IEC 60068-2-27
EMC immunity to interference	per EN 61000-6-2
EMC emission of interference	per EN 61000-6-4
Fire load	5.28 MJ



Commercial data		
Product Group	27 (special components I/O)	
PU (SPU)	1 pcs	
Packaging type	Box	
Country of origin	TW	
GTIN	4045454847593	
Customs tariff number	85176200000	

Product Classification		
UNSPSC	43222612	
eCl@ss 10.0	19-17-01-30	
eCl@ss 9.0	19-17-01-06	
ETIM 9.0	EC000734	
ETIM 10.0	EC000734	
ECCN	NO US CLASSIFICATION	

Environmental Product Compliance		
RoHS Compliance Status	Compliant, No Exemption	

Approvals / Certificates

General approvals			Declarations of conformity and manufacturer's declarations		
  					
Approval	Standard	Certificate Name	Approval	Standard	Certificate Name
EAC GZO Almaty Standart	TP TC 020/2011	EAC CoC 03083	EU-Declaration of Confor- mity WAGO GmbH & Co. KG	-	-
KC National Radio Research Agency	Article 58-2, Clause 3	MSIP-REM-W43-ISW852	UK-Declaration of Confor- mity WAGO GmbH & Co. KG	-	-
UL Underwriters Laboratories Inc. (ORDINARY LOCATI- ONS)	UL 508	E175199 Sec.7			

Approvals for marine applications

		
Approval	Standard	Certificate Name
DNV DNV GL SE	-	TAA0000239



Downloads

Environmental Product Compliance

Compliance Search
Environmental Product Compliance 852-111

Documentation

Manual
Product Manual 5-Port 100BASE-TX Industrial ECO Switch
V 1.3.1 14.07.2020
pdf 971.15 KB

Installation manual
Gebrauchs- und Montageanleitung 852-111 / 852-112
pdf 1692.81 KB

System Description
Industrial Switches – General Product Information
pdf 1873.93 KB

Bid Text			
852-111	19.02.2019	xml 5.13 KB	↓
852-111	09.10.2017	doc 27.00 KB	↓
ausschreiben.de 852-111			↓

CAD/CAE-Data

CAD data
2D/3D Models 852-111

CAE data
EPLAN Data Portal 852-111
WSCAD Universe 852-111
ZUKEN Portal 852-111

1 Compatible Products

1.1 Optional Accessories

1.1.1 Cables and connectors

1.1.1.1 Connector plug



Item No.: 750-979/000-011
Connector ETHERNET; RJ-45; Cat. 6A; angled; Code T568A; AWG 22; Strain relief



Item No.: 750-979/000-021
Connector ETHERNET; RJ-45; Cat. 6A; angled; Code T568A; AWG 24; Strain relief



Item No.: 750-979/000-012
Connector ETHERNET; RJ-45; Cat. 6A; angled; Code T568B; AWG 22; Strain relief



Item No.: 750-979/000-022
Connector ETHERNET; RJ-45; Cat. 6A; angled; Code T568B; AWG 24; Strain relief



Item No.: 750-977/000-011
Connector ETHERNET; RJ-45; Cat. 6A; straight; Code T568A; AWG 22



Item No.: 750-978/000-011
Connector ETHERNET; RJ-45; Cat. 6A; straight; Code T568A; AWG 22; Strain relief



Item No.: 750-977/000-021
Connector ETHERNET; RJ-45; Cat. 6A; straight; Code T568A; AWG 24



Item No.: 750-978/000-021
Connector ETHERNET; RJ-45; Cat. 6A; straight; Code T568A; AWG 24; Strain relief



1.1.1.1 Connector plug



Item No.: 750-977/000-012
Connector ETHERNET; RJ-45; Cat. 6A; straight; Code T568B; AWG 22



Item No.: 750-978/000-012
Connector ETHERNET; RJ-45; Cat. 6A; straight; Code T568B; AWG 22; Strain relief



Item No.: 750-977/000-022
Connector ETHERNET; RJ-45; Cat. 6A; straight; Code T568B; AWG 24



Item No.: 750-978/000-022
Connector ETHERNET; RJ-45; Cat. 6A; straight; Code T568B; AWG 24; Strain relief



Item No.: 750-979/000-013
Connector PROFINET; RJ-45; Cat. 6A; angled; AWG 22; Strain relief



Item No.: 750-977/000-013
Connector PROFINET; RJ-45; Cat. 6A; straight; AWG 22



Item No.: 750-978/000-013
Connector PROFINET; RJ-45; Cat. 6A; straight; AWG 22; Strain relief



Item No.: 750-975
ETHERNET RJ-45 connector, IP20; ETHERNET 10/100 Mbit/s; for field assembly



Item No.: 750-976
PROFINET RJ-45 connector, IP20; ETHERNET 10/100 Mbit/s; for field assembly

1.1.2 Installation

1.1.2.1 Mounting accessories



Item No.: 852-9101
DNV Carrier rail adapter; for ETHERNET Switches 852-111/ 852-1111 marine approval; -

1.1.3 Interface module

1.1.3.1 Interface module



Item No.: 289-195
Interface module; RJ-45; IDC technology; Cat. 6; in mounting carrier; with shield connection



Item No.: 289-175
Interface module; RJ-45; PCB terminal blocks, double-row; Cat. 5; in mounting carrier; with shield connection; with shield clamping saddle; 1,50 mm²



Item No.: 289-172
Interface module; RJ-45; RJ-45; Cat. 5; in mounting carrier



Item No.: 289-196
Interface module; RJ-45; with power jumper contacts; PCB terminal blocks; Cat. 5

1.1.4 Power supply

1.1.4.1 Power Supply



Item No.: 787-1102
Switched-mode power supply; Compact; 1-phase; 24 VDC output voltage; 1.3 A output current; DC-OK LED



Item No.: 787-1112
Switched-mode power supply; Compact; 1-phase; 24 VDC output voltage; 2.5 A output current; DC-OK LED



Item No.: 787-1122
Switched-mode power supply; Compact; 1-phase; 24 VDC output voltage; 4 A output current; DC-OK LED



Item No.: 787-1226
Switched-mode power supply; Compact; 1-phase; 24 VDC output voltage; 6 A output current; DC-OK LED



Item No.: 787-1702
Switched-mode power supply; Eco; 1-phase; 24 VDC output voltage; 1.25 A output current; DC-OK LED



Item No.: 787-1712
Switched-mode power supply; Eco; 1-phase; 24 VDC output voltage; 2.5 A output current; DC-OK LED



Item No.: 787-1722
Switched-mode power supply; Eco; 1-phase; 24 VDC output voltage; 5 A output current; DC-OK LED

Subject to changes. Please also observe the further product documentation!

Current addresses can be found at: www.wago.com