



# SHOP DRAWING

## HAND DRYER SHDL SERIES



## FEATURES

### COLOUR

white

### MANUFACTURING

- shell is a one-piece mold of Lexan 940
- secured to a zinc alloy wall bracket with two chrome-plated, tamper-proof bolts
- chrome-plated, die-cast zinc turbine forces air
- tamper-proof vent, preventing the insertion of foreign objects

### SOUND LEVEL

72 dBA

### ELEMENT

nichrome

### CONTROL

- SHDLAS model - an infrared optical sensor located next to the air outlet activates the hand dryer
- a 90-second lockout feature is activated if hands are not removed before this time
- SHDLPB model - push button start
- built-in 30-second sealed electronic timer

### INSTALLATION

wall mounted

