



Classic filament LEDbulbs

7.5A50/VIN/820/CL/G/D+CORD VIN

Philips LED vintage-style lamps allow you to maintain a warm, classic light effect while providing longer life and energy savings.

Product data

General Information	
Cap-Base	E26 [Single Contact Medium Screw]
Nominal Lifetime (Nom)	15000 h
Switching Cycle	20000X
Technical Type	7.5-40W

Light Technical	
Color Code	820 [CCT of 2000K]
Initial lumen (Nom)	400 lm
Luminous Flux (Rated) (Nom)	400 lm
Color Designation	Flame
Correlated Color Temperature (Nom)	2000 K
Luminous Efficacy (rated) (Nom)	53.00 lm/W
Color Consistency	<6
Color Rendering Index (Nom)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %

Operating and Electrical	
Input Frequency	50 to 60 Hz
Power (Rated) (Nom)	7.5 W
Lamp Current (Nom)	70 mA
Wattage Equivalent	40 W

Starting Time (Nom)	0.5 s
Warm Up Time to 60% Light (Nom)	0.5 s
Power Factor (Nom)	0.7
Voltage (Nom)	120 V


Temperature	
T-Case Maximum (Nom)	45 °C

Controls and Dimming	
Dimmable	Yes

Product Data	
Order product name	7.5A50/VIN/820/CL/G/D+CORD VIN
EAN/UPC - Product	046677539672
Order code	539676
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	2
Material Nr. (12NC)	929001936495
Net Weight (Piece)	0.660 kg

Classic filament LEDbulbs


Dimensional drawing




Bulb A160 120V 8-40W 450lm 2000K E26 D

Product	D	C
7.5A50/VIN/820/CL/G/D+CORD VIN	160 mm	292 mm


Photometric data



LEDbulb E26 40W





LEDbulb E26 G63 40W



LEDbulb E26 A50 40W

Classic filament LEDbulbs

Lifetime



LEDbulb E26

LEDbulb E26

