

Pilot and Signaling Devices

Heavy-Duty 22.5 mm Watertight/Oiltight Pilot Lights

C-2000

Standard

600 VAC Max., 300 VDC Max.

10 Amps Continuous AC, 2.5 Amps Continuous DC

Selection Process

Select operator below + Select power supply from page 9-92 & 9-93 + Select nameplate, if required, from pages 9-95 to 9-97 = Complete Unit



Standard Pilot Lights

Standard Operators

Operator Style	Lens Type	Power Supply Type	Product Number
Round Polished Chrome	Diffused	—	P9CL*D
Round Polished Chrome	Refracted	—	P9CL*R
Round Polished Chrome	Glass lens	—	P9CL*V
Round Polished Chrome	None	—	P9CL00
Round Satin Chrome	Diffused	—	P9ML*D
Round Satin Chrome	Refracted	—	P9ML*R
Round Satin Chrome	Glass lens	—	P9ML*V
Round Satin Chrome	None	—	P9ML00
Round Engineered Plastic	Diffused	—	P9XL*D
Round Engineered Plastic	Refracted	—	P9XL*R
Round Engineered Plastic	None	—	P9XL00
Square Engineered Plastic	Diffused	—	P9SL*D
Square Engineered Plastic	None	—	P9SL00
Unibloc	Diffused	Full Voltage-120 V	P9XU*DDO ¹
Unibloc	Refracted	Full Voltage-120 V	P9XU*RDO ¹
Unibloc	Diffused	Resistor-120 V	P9XU*DRN ¹
Unibloc	Refracted	Resistor-120 V	P9XU*RRN ¹
Unibloc	None	Full Voltage-120 V	P9XU00DO ¹
Unibloc	None	Resistor-120 V	P9XU00RN ¹

¹Available only as a pilot light, Unibloc combines an indicator light and power source in one unit, producing a savings for the customer. Full-voltage versions do not include lamp; select lamp from page 9-119. Resistor versions are 130V (ac/dc) and include BA9S 130 V/2W lamp.

Replace asterisk (*) in product number with color code digit from Colors table below.

*Colors

Color	Red	Green	Yellow	Blue	White	Orange	Clear
*Color Code	R	V	G	L	B	A	I

