

**15.3T8/CNG/48-850/
MX21/G 25/1**

929004351704



Contractor grade, LEDtube, T8, 1200 mm, 15.3 W, 5000 K, 2100 lm, 50000 hour(s)

Contractor grade, LEDtube, T8, 1200 mm, 15.3 W, 5000 K, 2100 lm, 50000 hour(s), 137 lm/W, G13, Glass, 0 %

General Information

Cap-Base	G13
Nominal lifetime	50,000 hour(s)
Switching Cycle	50,000
Lighting Technology	LEDtube

Light Technical

Color Code	850 [CCT of 5000K]
Beam Angle (Nom)	220 degree(s)
Luminous Flux	2,100 lm
Color Designation	Daylight
Correlated Color Temperature (Nom)	5000 K
Luminous Efficacy (rated) (Nom)	137 lm/W
Color Consistency	<5
Color rendering index (CRI)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %

Operating and Electrical

Input Frequency	50 to 60 Hz
Power Consumption	15.3 W
Lamp Current (Max)	168 mA
Lamp Current (Min)	63 mA
Wattage Equivalent	32 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.9
Voltage (Nom)	120-277 V
UL Type	UL Type B

Temperature

T-Case Maximum (Nom)	60 °C
----------------------	-------

Controls and Dimming

Dimmable	Limited
----------	---------

Mechanical and Housing

Bulb Finish	Frosted
Bulb Material	Glass
Product Length	1,200 mm
Bulb Shape	T8
Net Weight (Piece)	0.200 kg


Approval and Application

Energy Saving Product	Yes
Approval Marks	RoHS compliance
EU RoHS compliant	Yes
Ambient temperature range	-20 to +45 °C
Post-consumer recycled plastic material ratio	0 %

Application Conditions

can it be used in closed luminaires	Yes
Wireless Technology	Not applicable

Dimensional drawing



Sustainability Data



Product non-virgin material ratio	0 %
-----------------------------------	-----

Product Data

Order product name	15.3T8/CNG/48-850/MX21/G 25/1
Full product name	15.3T8/CNG/48-850/MX21/G 25/1
Order code	929004351704
Material Nr. (12NC)	929004351704
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677610333
Numerator - Packs per outer box	25
EAN/UPC - Case	50046677610338


Product	D1	D2	A1	A2	A3
15.3T8/CNG/48-850/MX21/G 25/1	25.7 mm	25.7 mm	1,199.4 mm	1,206.5 mm	1,213.6 mm

Photometric data




General uniform lighting - 15.3T8/CNG/48-850/MX21/G 25/1

Light Distribution Diagram - 15.3T8/CNG/48-850/MX21/G 25/1




Spectral Power Distribution Colour - 15.3T8/CNG/48-850/
MX21/G 25/1

Lifetime




Life Expectancy Diagram


Lumen Maintenance Diagram - 15.3T8/CNG/48-850/MX21/G 25/1



LifetimeVsTc



FailureRate



Lumen Maintenance Diagram - 15.3T8/CNG/48-850/MX21/G 25/1

Related Documents

Documents and certificates	Document Name	Download
Environmental Product Declaration	Philips-Contractor-Type-B-MainsFit-T8-COMF-9434870-Ref-929004351604-EPD.pdf	Download 
Installation Instructions	TLED-Type-B-T8-DE-SE-QIG-Online-Installation-INI.pdf	Download 
Photometry and lighting design	Document Name	Download
IES File	15-3T8-CNG-48-850-MX21-G-25-1-9290043517-IES.IES	Download 