

PHILIPS

**33PAR38/PER/835/F25/D
IM/120V 6/1FB**

929004431204



MasterClass, LEDspot, PAR38, 250 W, E26, 3500 K, 3000 lm, 25000 hour(s), Metal

MasterClass, LEDspot, PAR38, 250 W, E26, 3500 K, 3000 lm, 25000 hour(s), Metal, 90 lm/W

General Information

Cap-Base	E26
Nominal lifetime	25,000 hour(s)
Switching Cycle	50,000
Lighting Technology	LEDspot

Light Technical

Color Code	835 [CCT of 3500K]
Beam Angle (Nom)	25 degree(s)
Luminous Flux	3,000 lm
Luminous Intensity (Nom)	10,000 cd

Color Designation	White (WH)
Correlated Color Temperature (Nom)	3500 K
Luminous Efficacy (rated) (Nom)	90 lm/W
Color Consistency	<4
Color rendering index (CRI)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %

Operating and Electrical

Input Frequency	50 to 60 Hz
Power Consumption	33 W
Lamp Current (Nom)	300 mA
Wattage Equivalent	250 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.95
Voltage (Nom)	120 V

Temperature

T-Case Maximum (Nom)	90 °C
----------------------	-------


Controls and Dimming

Dimmable	Only with specific dimmers
----------	----------------------------

Mechanical and Housing

Bulb Finish	Clear
Bulb Material	Metal
Bulb Shape	PAR38
UL Wet/ damp/ dry location	Damp location
Net Weight (Piece)	0.560 kg

Dimensional drawing



Approval and Application

Suitable For Accent Lighting	Yes
EU RoHS compliant	Yes
T20 compliant	N/A
Ambient temperature range	-20 to +45 °C

Application Conditions


can it be used in closed luminaires	No
Wireless Technology	Not applicable

Product Data


Order product name	33PAR38/PER/835/F25/DIM/120V 6/1FB
Full product name	33PAR38/PER/835/F25/DIM/120V 6/1FB
Order code	929004431204
Material Nr. (12NC)	929004431204
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677610760
Numerator - Packs per outer box	6
EAN/UPC - Case	50046677610765

Product	D	C
33PAR38/PER/835/F25/DIM/120V 6/1FB	123 mm	133 mm

Photometric data




Spectral Power Distribution Colour - 33PAR38/PER/835/F25/DIM/120V 6/1FB




Light Distribution Diagram - 33PAR38/PER/835/F25/DIM/120V 6/1FB

Lifetime



Life Expectancy Diagram



Lumen Maintenance Diagram - 33PAR38/PER/835/F25/DIM/120V 6/1FB

Related Documents

Documents and certificates	Document Name	Download
Environmental Product Declaration	MASTER-LEDspot-PAR-High-Lumen-COMF-7373634-Ref-929004431104-EPD.pdf	Download
Photometry and lighting design	Document Name	Download
IES File	LEDspots-NAM1-33W-PAR38-E26-835-25D-IES.IES	Download

