

Product data sheet

Specifications



APC Back-UPS Pro, 1350VA/810W, Tower, 120V, 10x NEMA 5-15R outlets, Sine Wave, AVR, USB Type A + C ports, LCD, User Replaceable Battery

BR1350MS

Product availability: Non-Stock - Not normally stocked in distribution facility

Main

Main input voltage	120 V AC 1 phase
Input connection	NEMA 5-15P
Maximum input current	12 A
Switching current capacity	15 A
Plug standard	NEMA 5-15P
Efficiency at full load	88...147 V
Input frequency	60 Hz +/- 3 Hz
Output voltage	120 V AC 1 phase
Rated power in W	810 W
Rated power in VA	1350 VA
Output connection	6 NEMA 5-15R 4 NEMA 5-15R surge
Type of USB power supply	USB type A + C
Maximum configurable power in VA	1350 VA
Maximum configurable power in W	810 W
Transfer time	8ms typical : 10 ms maximum
UPS topology	Line Interactive
Waveform type	Sine wave
Output frequency	60 Hz +/- 3 Hz sync to mains
Replacement battery	APCRBC161

Graphs

Run Time	View Runtime Graph
Efficiency	View Efficiency Graph

Complementary

Battery type	Lead-acid internal included
Control panel	Multi-function LCD status and control console
UPS connectivity	USB port

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Surge energy rating	1080 J
Noise filtering	Full time multi-pole noise filtering :5% of IEEE surge let-through : zero clamping response time: in
Cable length	6 ft (1.8 m)
Number of cables	1
Height	10.2 in (260 mm)
Width	3.9 in (100 mm)
Depth	14.5 in (368 mm)
Product weight	25.8 lb(US) (11.7 kg)
Mounting preference	No preference
Mounting mode	Not rack-mountable
Two post mountable	0
USB compatible	Yes
Mounting mode	Tower
Number of power module filled slots	0
Number of power module free slots	0
Additional specification	Gaming performance
Redundant	No
Range of product	Back-UPS Pro
Product or component type	Uninterruptible power supply (UPS)

Environment

Product certification	ENERGY STAR V2.0 (USA) NOM TUV C-US certified
Equipment protection policy	Lifetime : \$500000
Ambient air temperature for operation	32...104 °F (0...40 °C)
Ambient air temperature for storage	5...104 °F (-15...40 °C)
Storage altitude	0...10000 ft (0...3048 m)
Relative humidity	0...95 % non-condensing
Storage relative humidity	0...95 % non-condensing
Acoustic level	45 dBA
Operating altitude	0...10000 ft

Batteries & Runtime

Battery type	Lead-Acid battery
Extendable runtime	0
Included battery module	1
Empty battery slot	0
Typical recharge time	16 h
RBC quantity	2
Battery life	3...5 year(s)

Battery charging power	10 W rated
------------------------	------------

Ordering and shipping details

Category	11309-APC RESALE PRODUCTS
Discount Schedule	APC1
GTIN	00731304335399
Returnability	No
Country of origin	PH

Packing Units

Unit Type of Package 1	PCE
Nbr. of units in pkg.	1
Package 1 Height	14.12 in (35.87 cm)
Package 1 Width	19.0 in (48.2 cm)
Package 1 Length	8.8 in (22.3 cm)
Package weight(Lbs)	29.3 lb(US) (13.3 kg)
SCC14	10731304335396

Contractual warranty

Warranty (in months)	36 UPS 12 Battery
----------------------	-------------------



Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)



Environmental footprint

Total lifecycle Carbon footprint	474 kg CO2 eq.
Carbon footprint of the manufacturing phase [A1 to A3]	127 kg CO2 eq.
Carbon footprint of the distribution phase [A4]	1 kg CO2 eq.
Carbon footprint of the installation phase [A5]	0 kg CO2 eq.
Carbon footprint of the use phase [B2, B3, B4, B6]	343 kg CO2 eq.
Carbon footprint of the end-of-life phase [C1 to C4]	1 kg CO2 eq.
Environmental Disclosure	Product Environmental Profile

Use Better



Materials and Substances

Average percentage of recycled plastic content	15 %
Packaging made with recycled cardboard	Yes
Packaging without single use plastic	No
SCIP Number	019b51cf-d7f1-4f06-ac85-1378fc94c7aa
EU RoHS Directive	Compliant By Exemption
REACH Regulation	Reference contains Substances of Very High Concern above the threshold
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov



Energy efficiency

Optimized Energy Efficiency	Energy efficient product
ENERGY STAR®	ENERGY STAR UPS V2.0 (USA)

Use Longer



Lifetime extension

Repair	No
--------	----

Use Again



Repack and remanufacture

Recyclability potential, in %	62
-------------------------------	----

Circularity Profile	End of Life Information
Removable battery	User replaceable
Take-back	Yes

Image of product / Alternate images

Alternative

