




THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.


PANDUIT PART NUMBER*	MAT'L SUFFIX	MATERIAL	"D"	REC. FAST. *	WEIGHT lbs/100 pcs (g)/100 pcs	USE WITH THESE CABLE TIE CROSS-SECTIONS
TA1S8	NONE	NYLON 6/6	0.17 [4.3]	#8 (M4) SCREW	0.07 [32.0]	MINIATURE INTERMEDIATE STANDARD
	-0	WEATHER RESISTANT NYLON				
	-30	HEAT STABILIZED NYLON				
	-69	FLAME RETARDANT NYLON				
TA1S10	NONE	NYLON 6/6	0.20 [5.1]	#10 (M5) SCREW		
	-0	WEATHER RESISTANT NYLON				



NOTES:

- *SEE www.panduit.com FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE, PART MATERIAL, PART COLOR AND ANY THIRD PARTY RECOGNITION OR COMPLIANCE
- HOLE DIMENSIONS SHOULD ACCOMMODATE SPECIFIED RECOMMENDED FASTENER.
- BAG MAY CONTAIN EXTRA PIECES TO COMPENSATE FOR VARIANCE IN THE PACKAGING PROCESS. PANDUIT ASSURES MINIMUM PIECE COUNT AS STATED ON THE BAG.

00A	09.21.2026	JADE	BWG	MRJS	b. REVISED NOTE 1. a. DRAWING COMPLETELY REVISED. WAS GB0239EP/03	038932/00
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN

TITLE					
TIE ANCHOR MOUNT					
CUSTOMER DRAWING					
ITEM REVISION NAME			PANDUIT		
02945NAL/00					
DATASET FILE NAME			MATERIAL:		
02945NAL_DC/00A					
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]			SEE TABLE		
.x ± 0.05 [1.3] .xxx ± 0.01 [0.25] .xx ± 0.02 [0.5] ANGLES ± 5 °					
			THIRD ANGLE PROJECTION		
DRAWN BY		DATE	CHK	SCALE	DRAWING NUMBER:
AJV		12/17/96	JADE	NONE	02945NAL_DC
				SHT 1 OF 1	SIZE
					A