
THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT PART #	MILITARY PART NO. AND CLASS	STUD SIZE	DIMENSIONS in. [mm]				
		ENG	L ± .08 [2.03]	W ± .01 [0,25]	C ± .02 [0,38]	M ± .06 [1.53]	H ± .01 [0,25]
PN14-4R	MS25036-152 CLASS 1	#4	.74[18.8]	.25[6.4]	.20[5.1]	.66[16.8]	.12[3.1]
PN14-6R	MS25036-107 CLASS 1	#6	.85[21.6]	.31[7.9]	.25[6.4]	.71[18.0]	.15[3.8]
PN14-6RN	MS25036-106 CLASS 1	#6	.76[19.3]	.25[6.4]	.20[5.1]	.63[16.0]	.15[3.8]
PN14-8R	MS25036-153 CLASS 1	#8	.85 [21.6]	.31 [7.9]	.25 [6.4]	.68 [17.3]	.17 [4,3]
PN14-10R	MS25036-108 CLASS 1	#10	.85[21.6]	.31[7.9]	.25[6.4]	.68 [17.3]	.20[5.1]
PN14-14R	MS25036-154 CLASS 1	1/4"	1.05[26.7]	.46[11.7]	.38[9.7]	.82[20.8]	.27[6.9]
PN14-56R	MS25036-109 CLASS 1	5/16"	1.05[26.7]	.46[11.7]	.38[9.7]	.82[20.8]	.34[8.6]
PN14-38R	MS25036-110 CLASS 1	3/8"	1.14 [29.0]	.53 [13.5]	.43 [10.9]	.86 [21.8]	.40 [10.2]
PN14-12R	----	1/2"	1.35 [34.3]	.72 [18.3]	.53 [13.5]	.99 [25.1]	.52 [13.2]



NOTES:

1. VISIT OUR ON-LINE CATALOG AT WWW.PANDUIT.COM FOR A LIST OF CURRENT PARTS APPLICABLE FOR USE WITH THIS PRODUCT.
2. DIMENSIONS IN [ ] ARE METRIC.
3. WEIGHT: .002 TO .004 Lbs. APROX
4. PART INCLUDES:
   A. STAMPING: .03" [0,8mm] THK COPPER, TIN PLATED
   B. HOUSING: NYLON, BLUE
   C. SLEEVE: BRASS, TIN PLATED
5. UL LISTED AND CSA CERTIFIED FOR:
   A. #18-14 AWG [1,5-2,5 mm²] SOLID OR STRANDED COPPER WIRE.
   B. 221°F [105°C] MAX. OPERATING TEMPERATURE.
   C. 600 V. MAX. VOLTAGE RATING
      1000 V. IN SIGNS, FIXTURES & LUMINARIES
6. WIRE STRIP LENGTH:
   7/32" $^{+1/32}_{-0}$ [5,6mm $^{+0,8}_{-0}$]

UL & CSA TOOLS (DIES)
CT-100
CT-1550
CT-1551
CT-2300 or Greenlee EK50ML
CT-2500 (CT-2550CH)

LISTED 587H E52164

CERTIFIED LR31212

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
13A	06-10-26	DPOI	DPOI	JSUN	-TOLERANCE FOR "L" CHANGED FROM 0.03" TO 0.08" & "G" CHANGED FROM 0.03" TO 0.06". - DIMENSION A CHANGED TO L. DIMENSION G CHANGED TO M. - MIN. WIRE INSULATION PONTING TO METAL I.D. CHANGED TO POINT TO PLASTIC I.D. FROM 0.162" TO 0.172". REMOVED MAX WIRE INSUL. - REMOVE MILITARY CLASS 2 & CT-600-A, CT-500CH, CT-525CH,CT-550CH,CT-570CH,CT-160,CT-400,CT-460, CT-250,CT-2400 - UPDATES TO LATESTS STANDARDS. - EDITED NOTES & REMOVE PK CHART.	026835/00
12	02-01-07	SHOR	-	-	MODIFIED NOTE #4, REMEOVED PACKAGE SIZES.	TR00214

PART NUMBER: SEE TABLE

TITLE: 3PC. NYLON ISULATED, #16-14 BARREL, RING TERMINAL

CUSTOMER DRAWING

ITEM REVISION NAME: N41185BA/13

DATASET FILE NAME: N41185BA-DC r13A

THIRD ANGLE PROJECTION

MATERIAL: SEE NOTE 4

DRAWING NUMBER: A41185

DRAWN BY	DATE	CHK	SCALE	SIZE
DPOI	05-12-26	RLS	-	A

SHEET 1 OF 1

A-SIZE CUSTOMER