

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT PART #	STUD SIZE		DIMENSIONS in. [mm]					TOOLS
	ENGLISH	METRIC	L ± .03 [0,8]	W ± .01 [0,25]	C ± .01 [0,38]	M ± .02 [0,8]	H ± .02 [0,5]	
PMNF1-3F	--	M3	.79 [20,0]	.23 [5,9]	.20 [5,2]	.65 [16,5]	.13 [3,3]	*CT-100, *CT-160, CT-250, *CT-260, *CT-400, CT-460, CT-1550, CT-1551, CT-2300, CT-2400 (CT-2455CH, CT-2455CHA, CT-2450CHA), CT-500CH, CT-550CH, CT-2500 (CT-2550CH)
PNF18-6F	#6	M3,5	.80 [20,3]	.30 [7,6]	.22 [5,6]	.66 [16,8]	.15 [3,8]	
PNF18-8F	#8	M4	.86 [21,8]	.31 [7,9]	.25 [6,4]	.69 [17,5]	.17 [4,3]	
PNF18-10F	#10	--	.87 [22,1]	.34 [8,6]	.26 [6,6]	.71 [18,0]	.20 [5,1]	
PMNF1-5F	--	M5	.90 [22,9]	.35 [8,9]	.25 [6,4]	.74 [18,8]	.21 [5,3]	
PNF18-14F	1/4"	M6	1.05 [26,7]	.44 [11,2]	.35 [8,9]	.80 [20,3]	.27 [6,9]	


*PANDUIT APPROVED TOOL

NOTES:


1. VISIT OUR ON-LINE CATALOG AT WWW.PANDUIT.COM FOR A LIST OF CURRENT PARTS APPLICABLE FOR USE WITH THIS PRODUCT.
2. DIMENSIONS IN [] ARE METRIC.
3. STANDARDS INFORMATION.
4. cULus LISTED FOR:
 - A. #22-18 AWG [0,5-1,0 mm²] STRANDED COPPER WIRE
 - B. 221°F [105°C] MAX. OPERATING TEMPERATURE
 - C. 600V. MAX. BLDG WIRE (1000 V. MAX. IN SIGNS, FIXTURES & LUMINAIRES)
5. MATERIAL:
 - A. STAMPING: .03" [0,8] THK COPPER, TIN PLATED
 - B. HOUSING: NYLON, RED
 - C. SLEEVE: BRASS, TIN PLATED

6. DIMENSIONS IN BRACKETS ARE METRIC EQUIVALENT

7. WIRE STRIP LENGTH: $7/32'' \begin{smallmatrix} +1/32 \\ -0 \end{smallmatrix}$ [5,6 $\begin{smallmatrix} +0,8 \\ -0 \end{smallmatrix}$]



11	01-27-26	RIAS	DPOI	JSUN	FOR PMNF1-3F: L DIM. WAS .83, M DIM. WAS .69. C TOLERANCE WAS $\pm .02$, M TOLERANCE WAS $\pm .03$, H TOLERANCE WAS $\pm .01$ NEW TITLE BLOCK FORMAT. TOOLS REMOVED: CT-600-A. ADDED: CT-250, CT-2300, CT-2400. NEW TITLE BLOCK FORMAT.	029619/00
10	06-14	MBY	JHNU	RGB	REVISED NOTES: MOVED TOOLS TO TABLE. REVISED CERTIFICATION.	A41260
09	12-12-13	JHNU	JHNU	RGB	REVISED NOTE 2B: C-550CH, CT-2550CH WAS CT-520CH, CT-2525	A41260
08	11-26-13	JHNU	TMR	RGB	INDICATE PNs NOT UL LISTED/CSA CERTIFIED	A41260
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN

PART NUMBER		SEE CHART			
TITLE					
FORK, NYLON (FUNNEL) INSULATED #22-18					
CUSTOMER DRAWING					
ITEM REVISION NAME			N41260BA/11		
DATASET FILE NAME			N41260BA_DC/11A		
			THIRD ANGLE PROJECTION		
MATERIAL			DRAWING NUMBER		
SEE NOTES			N41260BA		
DRAWN BY	DATE	CHK	SCALE	SHEET 1 OF 1	SIZE
DAW	-	LA	NONE		A